


# VIP-2/SC/D37SUB/M/SO - Termination board



2900786

<https://www.phoenixcontact.com/us/products/2900786>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and male D-SUB miniature pin strip, for mounting on NS 35 rails, 37-pos.

## Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters

## Commercial data

Item number	2900786
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK211H
GTIN	4046356545082
Weight per piece (including packing)	206 g
Weight per piece (excluding packing)	206 g
Customs tariff number	85366990
Country of origin	US

# VIP-2/SC/D37SUB/M/SO - Termination board



2900786

<https://www.phoenixcontact.com/us/products/2900786>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	37
No. of channels	16

### Electrical properties

Operating voltage (AC)	25 V AC
Operating voltage (DC)	60 V DC
Current (per branch)	≤ 2 A

Supported controller: HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TDIL01 (non-redundant)
	TDIL11 (redundant)
	TDOB01 (non-redundant)
	TDOB11 (redundant)
	TAIX01 (non-redundant)
	TAIX11 (redundant)
	TAOX01 (non-redundant)
	TAOX11 (redundant)

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

# VIP-2/SC/D37SUB/M/SO - Termination board



2900786

<https://www.phoenixcontact.com/us/products/2900786>

Width	101 mm
Height	65.5 mm
Depth	45.1 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# VIP-2/SC/D37SUB/M/SO - Termination board




2900786

<https://www.phoenixcontact.com/us/products/2900786>

## Drawings

Circuit diagram



Connection scheme VIP-2/SC/D37SUB/M/SO

# VIP-2/SC/D37SUB/M/SO - Termination board





2900786


<https://www.phoenixcontact.com/us/products/2900786>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2900786>

 <b>CSA</b> Approval ID: 2122203				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	105 V	2 A	28 - 14	-

 <b>cUL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	125 V	2 A	30 - 12	-

 <b>UL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	125 V	2 A	30 - 12	-

 <b>CSAus</b> Approval ID: 2122203				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	105 V	2 A	28 - 14	-

# VIP-2/SC/D37SUB/M/SO - Termination board



2900786

<https://www.phoenixcontact.com/us/products/2900786>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2900786

<https://www.phoenixcontact.com/us/products/2900786>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	25b23bc3-da0f-48f9-907d-c2a9da7184cd

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)