

FLKM-PA-D37/HW/AID4/C300 - Front adapter



2905321

<https://www.phoenixcontact.com/us/products/2905321>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE front adapter, for Honeywell C300, series C I/O, max. 1x 16 channels with configuration plug and 37-pos. D-SUB connector

Your advantages

- Preassembled system cables are connected directly to I/O modules using the front adapters
- Front adapter with D-SUB connector
- Prewired connector with configuration plug
- Connection of analog modules

Commercial data

Item number	2905321
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BMH
GTIN	4046356959384
Weight per piece (including packing)	115.7 g
Weight per piece (excluding packing)	99.99 g
Customs tariff number	85444290
Country of origin	DE

FLKM-PA-D37/HW/AID4/C300 - Front adapter



2905321

<https://www.phoenixcontact.com/us/products/2905321>

Technical data

Product properties

Product type	Front adapter
--------------	---------------

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Operating voltage (AC)	≤ 50 V AC
Operating voltage (DC)	≤ 60 V DC
Current (Per path)	≤ 1 A

Supported controller: HONEYWELL Experion PKS C300/C-Series

Suitable I/O card	TAIX01 (non-redundant)
	TAIX11 (redundant)
	TAIX51 (non-redundant)
	TAIX61 (redundant)
	TAIN01 (non-redundant)
	TAIN11 (redundant)

Connection data

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN EN 50178
	IEC 60664

Mounting

Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM-PA-D37/HW/AID4/C300 - Front adapter





2905321

<https://www.phoenixcontact.com/us/products/2905321>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905321>

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	1 A	30 - 12	-

FLKM-PA-D37/HW/AID4/C300 - Front adapter



2905321

<https://www.phoenixcontact.com/us/products/2905321>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

FLKM-PA-D37/HW/AID4/C300 - Front adapter



2905321

<https://www.phoenixcontact.com/us/products/2905321>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com