

EEM-MA600 - Measuring device



2901366

<https://www.phoenixcontact.com/us/products/2901366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Energy measurement device to measure electrical parameters in low voltage installations up to 700 V, acquisition of individual harmonic oscillations - can be extended with communication and special functional modules

Your advantages

- Can be extended with special function and communication modules
- Remote access via web server, integrated in Ethernet communication module
- Trend calculation for real and reactive power
- Acquisition of individual harmonics up to 63rd harmonic

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2901366 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C446 |
| Product key | CMMC11 |
| GTIN | 4046356584258 |
| Weight per piece (including packing) | 821.5 g |
| Weight per piece (excluding packing) | 821.5 g |
| Customs tariff number | 90303100 |
| Country of origin | TN |

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|--------------|-------------------------|
| Product type | Energy measuring device |
|--------------|-------------------------|

Electrical properties

| | |
|---|---|
| Electrical isolation | EN 61010-1 (Safe isolation) |
| | See extension module |
| | See extension module |
| Test voltage | 3.5 kV AC (50 Hz, 1 min.) |
| Maximum power dissipation for nominal condition | 10 VA |
| Mains type | 3-phase (3 or 4-conductor), 2-phase (2-conductor), and single-phase (1-conductor) |

Electrical isolation

| | |
|----------------------|---|
| Overvoltage category | III (For mains voltage <300 V AC (L/N)) |
| | II (for mains voltage >300 V AC ... 600 V AC (L/N)) |
| Pollution degree | 2 |

Supply

| | |
|---------------------------|---|
| Supply voltage | 230 V AC |
| | 400 V AC |
| Supply voltage range | 110 V AC ... 400 V AC ± 10 % |
| | 120 V DC ... 350 V DC (± 20 %) |
| Nominal power consumption | 10 VA |
| Power consumption | 20 VA (with max. number of extension modules) |

Input data

Measuring data acquisition

| | |
|--------------------------|-------------------------------|
| Measuring principle | True r.m.s. value measurement |
| Measured value | AC sine (50 Hz/60 Hz) |
| Acquisition of harmonics | up to 63rd harmonic |

Measurement: Voltage

| | |
|---------------------|--|
| Input name | Voltage measuring input V1, V2, V3 |
| Input voltage | 500 kV AC (Primary (via external voltage transducers)) |
| | Secondary: 60, 100, 110, 115, 120, 173, 190 V AC |
| Input voltage range | 18 V AC ... 700 V AC (Phase/Phase) |
| | 11 V AC ... 404 V AC (Phase/neutral conductor) |

EEM-MA600 - Measuring device



2901366

<https://www.phoenixcontact.com/us/products/2901366>

| | |
|-----------|-------|
| Precision | 0.2 % |
|-----------|-------|

Measurement: Current

| | |
|---|--|
| Input name | Current measurement I1, I2, I3 |
| Input current range | via external transformers |
| Input current | 9999 A (primary) 1 A and 5 A, secondary |
| Measuring range | 0 A ... 9999 A |
| Overload capacity | 6 A (Permanent) |
| Response threshold from measuring range nominal value | 10 mA |
| Precision | 0.2 % |
| Current overload | 10 x I _N for 1 s |

Measurement: Power

| | |
|-------------------------------|--|
| Messbereich_Leistung | 0 MW ... 8000 MW 0 Mvar ... 8000 Mvar 0 MVA ... 8000 MVA |
| Precision | 0.5 % |
| Active energy (IEC 62053-22) | Class 0.5 S |
| Reactive power (IEC 62053-23) | Class 2 |

Digital

| | |
|----------------------|---------------------|
| Voltage input signal | Via function module |
|----------------------|---------------------|

Output data

| | |
|--------------------|---------------------|
| Output description | Via function module |
|--------------------|---------------------|

Connection data

| | |
|----------------------------------|---|
| Connection method | COMBICON plug-in screw terminal block |
| Note | Connections for current, voltage, and supply |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Connection method | Screw connection |
| Note | Connections for digital I/O and communication |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |

Dimensions

| | |
|--------|--|
| Width | 96 mm |
| Height | 96 mm |
| Depth | 82 mm 80 mm (Installation depth with extension module) 60 mm (Installation depth without extension module) |

Material specifications

| | |
|-------|------------------|
| Color | black (RAL 9005) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------------------------|
| Degree of protection | (Front) |
| | IP30 (On the rear) |
| Ambient temperature (operation) | -10 °C ... 55 °C (14 °F ... 131 °F) |
| Ambient temperature (storage/transport) | -20 °C ... 85 °C (-4 °F ... 185 °F) |
| Max. permissible relative humidity (operation) | ≤ 95 % |
| Max. salt spray content | ≤ 2.5 % |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

UL, USA/Canada

| | |
|----------------|-----------------------|
| Identification | UL 61010-1 |
| | CSA-C22.2 No. 61010-1 |
| | cULus |

UL data

| | |
|--|---|
| Nominal supply voltage range | 110 V AC ... 240 V AC ±10 % |
| | 120 V DC ... 250 V DC ±10 % |
| Power consumption | 10 VA |
| Altitude | ≤ 2000 m |
| Operating mode | Indoor use |
| Surge voltages | transient overvoltage according to installation classes |
| Overvoltage category | I, II, III |
| Overvoltage category of the supply | Min. II |
| Ambient temperature (operation) | 0 °C ... 40 °C |
| Max. permissible relative humidity (operation) | 80 % (up to 31 °C) |
| | 50 % (at 40 °C) |

UL data

| | |
|--|---|
| Nominal supply voltage range | 110 V AC ... 240 V AC ±10 % |
| | 120 V DC ... 250 V DC ±10 % |
| Power consumption | 10 VA |
| Altitude | ≤ 2000 m |
| Operating mode | Indoor use |
| Ambient temperature (operation) | 0 °C ... 40 °C |
| Max. permissible relative humidity (operation) | 80 % (up to 31 °C) |
| | 50 % (at 40 °C) |
| Surge voltages | transient overvoltage according to installation classes |
| Overvoltage category | I, II, III |
| Overvoltage category of the supply | Min. II |

EEM-MA600 - Measuring device



2901366

<https://www.phoenixcontact.com/us/products/2901366>

Mounting

Mounting position

Front panel installation, horizontal

EEM-MA600 - Measuring device

2901366

<https://www.phoenixcontact.com/us/products/2901366>



Classifications

ETIM

ETIM 9.0

EC002301

EEM-MA600 - Measuring device



2901366

<https://www.phoenixcontact.com/us/products/2901366>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com