

PT-IQ-PTB-BE-UT - Surge protection base-element



2905364

<https://www.phoenixcontact.com/us/products/2905364>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element for the PLUGTRAB PT-IQ-PTB... supply and remote signaling module



Product description

DIN rail connector not included with delivery of PT-IQ basic element (PT-IQ-17,5-TBUS-5-2.0). Required DIN rail connectors must be ordered separately.

Commercial data

Item number	2905364
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL22
Product key	CL2151
GTIN	4046356959506
Weight per piece (including packing)	85.766 g
Weight per piece (excluding packing)	62 g
Customs tariff number	85366990
Country of origin	DE

PT-IQ-PTB-BE-UT - Surge protection base-element

2905364

<https://www.phoenixcontact.com/us/products/2905364>

Technical data

Product properties

Product type	Base element
Product family	PLUGTRAB IQ
Type	Base element, DIN rail mounting
Number of positions	1

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Supply: Status indicator/remote signaling

Operating voltage	20 V DC ... 30 V DC
Rated current	max. 130 mA (24 V DC)
	max. 160 mA (20 V DC)
Max. required back-up fuse	500 mA (T)
Number of surge protection modules that can be mounted side by side	28 (32 °C)


Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Ex data

Altitude	≤ 2000 m (amsl)
Ambient temperature (operation)	-40 °C ... 50 °C (T6)
	-40 °C ... 70 °C (T4)
Number of surge protection modules that can be mounted side by side	max. 10
Operating voltage	20 V DC ... 30 V DC
max. input voltage U_m	35 V DC
Maximum switching voltage U_m	60 V DC

Dimensions

Dimensional drawing	
---------------------	--

PT-IQ-PTB-BE-UT - Surge protection base-element



2905364

<https://www.phoenixcontact.com/us/products/2905364>

Width	17.7 mm
Height	91.1 mm
Depth	51.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

Material specifications

Color	black (RAL 9005)
	gray (RAL 7042)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Surge protection fault message	Remote indication contact
Max. required back-up fuse	500 mA (F)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 4000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %

Standards and regulations

Standards/specifications	EN 61000-6-2
Note	2005
Standards/specifications	EN 61000-6-3
Note	2007 + A1:2011
Standards/specifications	EN 60950-1
Note	2006 + A1:2010
Standards/specifications	EN 60079-0
Note	2018
Standards/specifications	EN 60079-11
Note	2012
Standards/specifications	EN 60079-15
Note	2010
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-11
Note	2011

PT-IQ-PTB-BE-UT - Surge protection base-element



2905364

<https://www.phoenixcontact.com/us/products/2905364>

Standards/specifications	IEC 60079-15
Note	2010
Standards/specifications	GB/T 3836.1
Note	2021
Standards/specifications	GB/T 3836.3
Note	2021
Standards/specifications	GB/T 3836.4
Note	2021
Standards/specifications	GB/T 3836.8
Note	2021

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

PT-IQ-PTB-BE-UT - Surge protection base-element





2905364

<https://www.phoenixcontact.com/us/products/2905364>

Drawings

Dimensional drawing



2905364

<https://www.phoenixcontact.com/us/products/2905364>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905364>



IECEx

Approval ID: IECEx BVS 14.0017X



cUL Listed

Approval ID: FILE E 333250



UL Listed

Approval ID: FILE E 333250



ATEX

Approval ID: BVS 14 ATEX E 020 X



NEPSI-EX

Approval ID: GYJ20.1158X



CCC

Approval ID: 2020322316001010



UKCA-EX

Approval ID: DEKRA 23UKEX0111X

PT-IQ-PTB-BE-UT - Surge protection base-element



2905364

<https://www.phoenixcontact.com/us/products/2905364>

Classifications

ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

ETIM

ETIM 10.0	EC001466
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

2905364

<https://www.phoenixcontact.com/us/products/2905364>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b0f8ce7a-4eb6-438d-bca6-ed73beffde91

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com