


FOC-PN-B-1000/IP20/... - FO patch cable



2901551

<https://www.phoenixcontact.com/us/products/2901551>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



POF PROFINET installation cable for assembly (IP20 heads only) for installation in stationary systems and machines, individual elements of polyamide (PA), halogen-free, ozone- and UV-resistant, with reinforced polyurethane (PUR) outer sheath

Your advantages

- Universal installation cable for installation in stationary systems and machines
- For indoors
- 2.2 mm individual wires made from extremely hard-wearing polyamide (PA)
- Rugged polyurethane (PUR) outer sheath
- PROFINET type B
- Halogen-free, ozone, and UV resistant

Commercial data

Item number	2901551
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC241
Country of origin	DE

Technical data

Product properties

Product type	Data cable preassembled
Application	Standard
Number of positions	2

Interfaces

Signal	PROFINET
	Modbus
	PROFIBUS

Electrical properties

Transmission speed	100 Mbps
--------------------	----------

Material specifications

Material Separating film	Aluminum
--------------------------	----------

Cable/line

Cable length	Free input (0.4 ... 100 m)
Cable weight	49 kg/km
External cable diameter	8 mm
Outer sheath, material	PUR
External sheath, color	green
External sheath, strain relief elements	Non-metallic, aramide fiber
Single wire, material	PA
Individual wire diameter	2.2 mm ±0.07 mm
Single wire, color	black and orange with arrow labeling
Tensile strength short-term/long-term	1000 N / 100 N
Lateral pressure short term	200 N/cm
Lateral pressure, long-term	20 N/cm
Impact strength	2 Nm / 10 x
Bending radius, single element	30 mm (Short-term)
	30 mm (Short-term)
Bending radius, entire cable	65 mm (Short-term)
	65 mm (Short-term)
660 nm	230 dB/km
Halogen-free	According to IEC 60754-2
Resistance to oil	IRM 902 No.2, 100 °C, DIN VDE 0473-811-2-1
Behavior in fire	1.62 MJ/m (0.39 kWh/m)

Environmental and real-life conditions

Ambient conditions

FOC-PN-B-1000/IP20/... - FO patch cable



2901551

<https://www.phoenixcontact.com/us/products/2901551>

Altitude	5000 m
----------	--------

FOC-PN-B-1000/IP20/... - FO patch cable



2901551

<https://www.phoenixcontact.com/us/products/2901551>

Classifications

ECLASS

ECLASS-13.0

27061803

UNSPSC

UNSPSC 21.0

26121600

FOC-PN-B-1000/IP20/... - FO patch cable



2901551

<https://www.phoenixcontact.com/us/products/2901551>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com