

# PT-IQ-5-EX-BE-UT - Surge protection base-element




2905497

<https://www.phoenixcontact.com/us/products/2905497>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element for protective plug PLUGTRAB PT-IQ-2X2-EX



## Product description

DIN rail connector not included with delivery of PT-IQ basic element (PT-IQ-17,5-TBUS-5-2.0). Required DIN rail connectors must be ordered separately.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2905497       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL22          |
| Product key                          | CL2152        |
| GTIN                                 | 4046356958189 |
| Weight per piece (including packing) | 90.5 g        |
| Weight per piece (excluding packing) | 62 g          |
| Customs tariff number                | 85363010      |
| Country of origin                    | DE            |

## Technical data

### Notes

#### General

|      |  |
|------|--|
| Note | <p>This item is a replacement base element for accommodating surge protection plugs from the PLUGTRAB PT-IQ product family (note compatibility).</p> <p>The base element contains the contacts that convey the remote signaling and power supply to the protective plug.</p> |
|------|--|

### Product properties

|                     |                                 |
|---------------------|---------------------------------|
| Product type        | Base element                    |
| Product family      | PLUGTRAB IQ                     |
| Type                | Base element, DIN rail mounting |
| Number of positions | 5                               |


#### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Screw thread                     | M3  |
| Tightening torque                | 0.5 Nm                                      |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section AWG      | 24 ... 14                                   |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 17.7 mm  |
| Height              | 91.1 mm  |
| Depth               | 51.6 mm  |
| Horizontal pitch    | 1 Div.   |

### Material specifications

|  |   |
|--|---|
| Color                                  | <p>blue (RAL 5015)</p> <p>gray (RAL 7042)</p> |
| Flammability rating according to UL 94 | V-0   |
| Housing material                       | PA 6.6  |

### Mechanical properties

# PT-IQ-5-EX-BE-UT - Surge protection base-element



2905497

<https://www.phoenixcontact.com/us/products/2905497>

## Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Protective circuit

|                                |                        |
|--------------------------------|------------------------|
| Rated current                  | 350 mA                 |
| Resistance per path            | 1.2 $\Omega$ $\pm$ 5 % |
| Surge protection fault message | none                   |

## Environmental and real-life conditions

### Ambient conditions

|   |                                      |
|---|--------------------------------------|
| Degree of protection                    | IP20 (with inserted protective plug) |
| Ambient temperature (operation)         | -40 °C ... 70 °C                     |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                     |
| Altitude                                | $\leq$ 2000 m (amsl)                 |

## Standards and regulations

|                          |              |
|--------------------------|--------------|
| Standards/specifications | EN 61643-21  |
| Note                     | A2:2013      |
| Standards/specifications | IEC 61643-21 |
| Note                     | A2:2012      |
| Standards/specifications | EN 60079-0   |
| Note                     | 2018         |
| Standards/specifications | EN 60079-11  |
| Note                     | 2012         |
| Standards/specifications | EN 60079-15  |
| Note                     | 2010         |
| Standards/specifications | IEC 60079-0  |
| Note                     | 2017         |
| Standards/specifications | IEC 60079-11 |
| Note                     | 2011         |
| Standards/specifications | IEC 60079-15 |
| Note                     | 2010         |
| Standards/specifications | GB/T 3836.1  |
| Note                     | 2021         |
| Standards/specifications | GB/T 3836.3  |
| Note                     | 2021         |
| Standards/specifications | GB/T 3836.4  |
| Note                     | 2021         |
| Standards/specifications | GB/T 3836.8  |
| Note                     | 2021         |

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

# PT-IQ-5-EX-BE-UT - Surge protection base-element




2905497

<https://www.phoenixcontact.com/us/products/2905497>

## Drawings

Dimensional drawing



2905497

<https://www.phoenixcontact.com/us/products/2905497>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905497>



### UL Listed

Approval ID: FILE E 138168



### IECEX

Approval ID: IECEX BVS 14.0017X



### cUL Listed

Approval ID: FILE E 333250



### UL Listed

Approval ID: FILE E 333250



### ATEX

Approval ID: BVS 14 ATEX E 020 X



### NEPSI-EX

Approval ID: GYJ20.1158X



### CCC

Approval ID: 2020322316001010



### UKCA-EX

Approval ID: DEKRA 23UKEX0111X

2905497

<https://www.phoenixcontact.com/us/products/2905497>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171502 |
| ECLASS-15.0 | 27171502 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001466 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

2905497

<https://www.phoenixcontact.com/us/products/2905497>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 6(c), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | d0b4f570-af65-4e23-b0a7-ce2d95fac139 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)