


FOC-GDM-RUGGED-1016/IP20/... - FO patch cable



2901558

<https://www.phoenixcontact.com/us/products/2901558>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Robust GOF installation cable for assembly (IP20 heads only) for installation in stationary systems and machines, aramid strain-relief elements, with individual elements made from FRNC material, halogen-free, ozone and UV resistant, with a polyurethane (PUR) outer sheath

Your advantages

- Robust installation cable for installation in stationary systems and machines
- For indoors
- Rugged polyurethane (PUR) outer sheath
- 2.9 mm individual wires made from highly flexible FRNC material
- Highly tear-resistant aramid strain relief elements
- Halogen-free, ozone, and UV resistant

Commercial data

Item number	2901558
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DN35
Product key	DNC243
Weight per piece (including packing)	1,220 g
Weight per piece (excluding packing)	1,220 g
Customs tariff number	85447000
Country of origin	DE

2901558

<https://www.phoenixcontact.com/us/products/2901558>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Data cable preassembled
Application	Standard
Number of positions	2

Interfaces

Signal	Modbus
	Ethernet
	PROFIBUS

Electrical properties

Transmission speed	1 Gbps
--------------------	--------

Mechanical properties

Tensile strength short-term/long-term	1000 N / 200 N
---------------------------------------	----------------

Cable/line

Cable length	Free input (1.0 ... 2000 m)
Cable weight	50 kg/km
External cable diameter	8 mm
Outer sheath, material	PUR
Single wire, material	FRNC material
Individual wire diameter	2.9 mm ±0.1 mm
Tensile strength short-term/long-term	1000 N / 200 N
Lateral pressure short term	400 N/cm
Lateral pressure, long-term	100 N/cm
Impact strength	2 Nm / 10 x
Bending radius, single element	30 mm (Short-term)
	30 mm (Short-term)
Bending radius, entire cable	65 mm (Short-term)
	65 mm (Short-term)
850 nm	2.5 dB/km
1300 nm	0.7 dB/km
Halogen-free	According to IEC 60754-2

2901558

<https://www.phoenixcontact.com/us/products/2901558>

Classifications

ECLASS

ECLASS-13.0	27061803
ECLASS-15.0	27061803

ETIM

ETIM 9.0	EC000034
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

2901558

<https://www.phoenixcontact.com/us/products/2901558>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com