

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monitoring relay for monitoring the phase sequence, phase failure and asymmetry of 3-phase voltages at 208 V AC ... 690 V AC, 2 changeover contacts, with screw connection

Product description

Increasingly higher demands are being placed on safety and system availability - across all sectors. Processes are becoming more and more complex, not only in mechanical engineering and the chemical industry, but also in plant and automation technology. Demands on power engineering are also increasing constantly.

Error-free and therefore cost-effective operation can only be achieved through continuous monitoring of important network and system parameters. Electronic monitoring relays in the EMD series are available for a wide range of monitoring tasks to avoid the consequences of errors or to keep them within limits.

The operating states are indicated using colored LEDs, errors that may occur can be sent to a control system via a floating contact or can shut down a part of the system. Some device versions are equipped with startup and response delays in order to briefly tolerate measured values outside the set monitoring range.

Commercial data

Item number	2905597
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK6631
GTIN	4046356967198
Weight per piece (including packing)	158 g
Weight per piece (excluding packing)	154.3 g
Customs tariff number	85364900
Country of origin	AT

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Technical data

Product properties

Product type	Phase monitoring relay
Operating mode	100% operating factor
Mechanical service life	20x 10 ⁶ cycles

Insulation characteristics

Overvoltage category	III
Pollution degree	3

Electrical properties

Service life electrical	2x 10 ⁵ cycles
Mains type	3-phase
Rated insulation voltage	250 V (Output circuit)
Rated surge voltage	6 kV

Supply

Supply voltage	±15 % (= measuring voltage)
Nominal power consumption	2 VA (1.2 W)

Input data

Input name	Measuring input
Measured value	AC sine (48 Hz ... 63 Hz)
Nominal input voltage U _N	690 V (3~ 208 V ... 690 V)
Input voltage range	177 V ... 794 V (3~)
Maximum input voltage	3~ 794 V
Frequency range	48 Hz ... 63 Hz
Setting range for response delay	0.1 s ... 10 s
Min setting range of the voltage threshold value	177 V AC
Max. setting range of the voltage threshold value	794 V AC
Function	Undervoltage Phase sequence Phase failure
Basic accuracy	≤ 3 % (of scale end value)
Setting accuracy	≤ 5 % (of scale end value)
Repeat accuracy	≤ 2 %
Asymmetry	25 %
Recovery time	> 500 ms

Output data

Switching

Contact switching type	2 floating changeover contacts
Maximum switching voltage	400 V AC

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Interrupting rating (ohmic load) max.	1250 VA (5 A/250 V AC at +55 °C)
	150 VA (5 A/30 V DC at +55°C)
	75 VA (2.5 A/30 V DC at +70°C)
Output fuse	5 A (fast-blow)

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.5 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section AWG	20 ... 14

Signaling

Status display	LED (yellow)
Operating voltage display	Green LED
Error indication	Red LED

Dimensions

Width	22.5 mm
Height	90 mm
Depth	113 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA, self-extinguishing

Environmental and real-life conditions

Ambient conditions

Degree of protection (Housing)	IP40 (Housing)
Degree of protection (Connection terminal blocks)	IP20 (Connection terminal blocks)
Ambient temperature (operation)	-25 °C ... 70 °C (C300)
	-25 °C ... 55 °C (B300)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Climatic class	3K3 (in acc. with EN 60721)
Permissible humidity (operation)	15 % ... 85 %

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UL, USA/Canada

Identification	UL/C-UL Listed UL 508
----------------	-----------------------

EMC data

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61326-1

Noise emission

Standards/regulations	EN 61326-1
-----------------------	------------

Standards and regulations

Standards/regulations	IEC 60664-1
-----------------------	-------------

Mounting

Mounting type	DIN rail mounting
Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any

EMD-SL-PH-690 - Monitoring relay




2905597

<https://www.phoenixcontact.com/us/products/2905597>

Drawings

Block diagram



EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905597>



EAC

Approval ID: RU*C-DE.*08.B.00010



UL Listed

Approval ID: FILE E 172140



cUL Listed

Approval ID: FILE E 172140

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Classifications

ECLASS

ECLASS-13.0	27371803
ECLASS-15.0	27371803

ETIM

ETIM 10.0	EC001441
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	5.325 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com