

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Monitoring relay for monitoring the phase sequence, phase failure and asymmetry of 3-phase voltages at 208 V AC ... 690 V AC, 2 changeover contacts, with screw connection

## Product description

Increasingly higher demands are being placed on safety and system availability - across all sectors. Processes are becoming more and more complex, not only in mechanical engineering and the chemical industry, but also in plant and automation technology. Demands on power engineering are also increasing constantly.

Error-free and therefore cost-effective operation can only be achieved through continuous monitoring of important network and system parameters. Electronic monitoring relays in the EMD series are available for a wide range of monitoring tasks to avoid the consequences of errors or to keep them within limits.

The operating states are indicated using colored LEDs, errors that may occur can be sent to a control system via a floating contact or can shut down a part of the system. Some device versions are equipped with startup and response delays in order to briefly tolerate measured values outside the set monitoring range.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2905597       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C440          |
| Product key                          | DK6631        |
| GTIN                                 | 4046356967198 |
| Weight per piece (including packing) | 158 g         |
| Weight per piece (excluding packing) | 154.3 g       |
| Customs tariff number                | 85364900      |
| Country of origin                    | AT            |

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

## Technical data

### Product properties

|                         |                            |
|-------------------------|----------------------------|
| Product type            | Phase monitoring relay     |
| Operating mode          | 100% operating factor      |
| Mechanical service life | 20x 10 <sup>6</sup> cycles |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 3   |

### Electrical properties

|                          |                           |
|--------------------------|---------------------------|
| Service life electrical  | 2x 10 <sup>5</sup> cycles |
| Mains type               | 3-phase                   |
| Rated insulation voltage | 250 V (Output circuit)    |
| Rated surge voltage      | 6 kV                      |

### Supply

|                           |                             |
|---------------------------|-----------------------------|
| Supply voltage            | ±15 % (= measuring voltage) |
| Nominal power consumption | 2 VA (1.2 W)                |

### Input data

|   |   |
|---|---|
| Input name  | Measuring input                                 |
| Measured value                                    | AC sine (48 Hz ... 63 Hz)                       |
| Nominal input voltage U <sub>N</sub>              | 690 V (3~ 208 V ... 690 V)                      |
| Input voltage range                               | 177 V ... 794 V (3~)                            |
| Maximum input voltage                             | 3~ 794 V  |
| Frequency range                                   | 48 Hz ... 63 Hz                                 |
| Setting range for response delay                  | 0.1 s ... 10 s                                  |
| Min setting range of the voltage threshold value  | 177 V AC  |
| Max. setting range of the voltage threshold value | 794 V AC  |
| Function  | Undervoltage<br>Phase sequence<br>Phase failure |
| Basic accuracy                                    | ≤ 3 % (of scale end value)                      |
| Setting accuracy                                  | ≤ 5 % (of scale end value)                      |
| Repeat accuracy                                   | ≤ 2 %   |
| Asymmetry   | 25 %  |
| Recovery time                                     | > 500 ms  |

### Output data

#### Switching

|                           |                                |
|---------------------------|--------------------------------|
| Contact switching type    | 2 floating changeover contacts |
| Maximum switching voltage | 400 V AC                       |

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Interrupting rating (ohmic load) max. | 1250 VA (5 A/250 V AC at +55 °C) |
|                                       | 150 VA (5 A/30 V DC at +55°C)    |
|                                       | 75 VA (2.5 A/30 V DC at +70°C)   |
| Output fuse                           | 5 A (fast-blow)                  |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Stripping length                 | 8 mm  |
| Conductor cross-section rigid    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 20 ... 14                                   |

## Signaling

|                           |              |
|---------------------------|--------------|
| Status display            | LED (yellow) |
| Operating voltage display | Green LED    |
| Error indication          | Red LED      |

## Dimensions

|        |         |
|--------|---------|
| Width  | 22.5 mm |
| Height | 90 mm   |
| Depth  | 113 mm  |

## Material specifications

|                             |                                  |
|-----------------------------|----------------------------------|
| Color                       | green (RAL 6021)                 |
| Housing insulation material | Polyamide PA, self-extinguishing |

## Environmental and real-life conditions

### Ambient conditions

|   |                                   |
|---|-----------------------------------|
| Degree of protection (Housing)                    | IP40 (Housing)                    |
| Degree of protection (Connection terminal blocks) | IP20 (Connection terminal blocks) |
| Ambient temperature (operation)                   | -25 °C ... 70 °C (C300)           |
|   | -25 °C ... 55 °C (B300)           |
| Ambient temperature (storage/transport)           | -25 °C ... 70 °C                  |
| Climatic class                                    | 3K3 (in acc. with EN 60721)       |
| Permissible humidity (operation)                  | 15 % ... 85 %                     |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UL, USA/Canada

|                |                       |
|----------------|-----------------------|
| Identification | UL/C-UL Listed UL 508 |
|----------------|-----------------------|

## EMC data

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive         |
| Low Voltage Directive         | Conformance with Low Voltage Directive |
| Noise immunity                | EN 61326-1                             |

## Noise emission

|                       |            |
|-----------------------|------------|
| Standards/regulations | EN 61326-1 |
|-----------------------|------------|

## Standards and regulations

|                       |             |
|-----------------------|-------------|
| Standards/regulations | IEC 60664-1 |
|-----------------------|-------------|

## Mounting

|                   |  |
|-------------------|--|
| Mounting type     | DIN rail mounting                                      |
| Assembly note     | on standard DIN rail NS 35 in accordance with EN 60715 |
| Mounting position | any  |

# EMD-SL-PH-690 - Monitoring relay




2905597

<https://www.phoenixcontact.com/us/products/2905597>

## Drawings

Block diagram



# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905597>



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010



**UL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: FILE E 172140

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371803 |
| ECLASS-15.0 | 27371803 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001441 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

# EMD-SL-PH-690 - Monitoring relay



2905597

<https://www.phoenixcontact.com/us/products/2905597>

## Environmental product compliance

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 5.325 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)