

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Preassembled relay module with screw connection, consisting of: relay base, relay retaining bracket, and power contact relay with test button, integrated status LED, and freewheeling diode. Contact switching type: 1 changeover contact. Input voltage: 24 V DC

## Product description

The pluggable electromechanical and solid-state relays in the RIFLINE complete product range and the base are recognized and approved in accordance with UL 508. The relevant approvals can be called up at the individual components in question.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2905659       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C465          |
| Product key                          | DK6519        |
| GTIN                                 | 4046356983266 |
| Weight per piece (including packing) | 69.11 g       |
| Weight per piece (excluding packing) | 68.86 g       |
| Customs tariff number                | 85364110      |
| Country of origin                    | CN            |

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

## Set consists of

### RIF-1-BSC/2X21 - Relay base

2900930

<https://www.phoenixcontact.com/us/products/2900930>



RIF-1... relay base, for miniature power relay with 1 or 2 changeover contacts or identical solid-state relays, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

---

### REL-MR- 24DC/21HC/MS - Single relay

2987888

<https://www.phoenixcontact.com/us/products/2987888>



Plug-in miniature relay, with power contact, 1 changeover contact, test button, mechanical switching position indicator, status LED, freewheeling diode, polarity A1+, A2-, input voltage 24 V DC

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

## RIF-RH-1-H - Retaining bracket

2904468

<https://www.phoenixcontact.com/us/products/2904468>



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-1 relay base, for 25 mm tall miniature power relay and solid-state relay

## Technical data

### Product properties

|                         |                                |
|-------------------------|--------------------------------|
| Product type            | Relay Module                   |
| Product family          | RIFLINE complete               |
| Application             | Palm switch                    |
| Operating mode          | 100% operating factor          |
| Mechanical service life | approx. $5 \times 10^6$ cycles |

### Insulation characteristics

|                      |  |
|----------------------|--|
| Insulation           | Safe isolation between input and output          |
|                      | Basic insulation between the changeover contacts |
| Overvoltage category | III  |
| Pollution degree     | 2  |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 12.09.2025 |
|------------------------------|------------|

### Electrical properties

|   |  |
|---|--|
| Service life electrical                         | see diagram  |
| Maximum power dissipation for nominal condition | 0.43 W   |
| Test voltage (Winding/contact)                  | 4 kV <sub>rms</sub> (50 Hz, 1 min., winding/contact) |
| Rated insulation voltage                        | 250 V AC   |
| Rated surge voltage                             | 6 kV (Input/output)                                  |
|   | 4 kV (between the changeover contacts)               |

### Input data

#### Coil side

|   |                               |
|---|-------------------------------|
| Nominal input voltage $U_N$               | 24 V DC                       |
| Input voltage range                       | 19.2 V DC ... 30 V DC (20 °C) |
| Input voltage range in reference to $U_N$ | see diagram                   |
| Drive and function                        | monostable                    |
| Drive (polarity)                          | polarized                     |
| Typical input current at $U_N$            | 18 mA                         |
| Typical response time                     | 9 ms                          |
| Typical release time                      | 10 ms                         |
| Coil voltage                              | 24 V DC                       |
| Protective circuit                        | Freewheeling diode            |
| Operating voltage display                 | Yellow LED                    |

### Output data

#### Switching

|                        |                      |
|------------------------|----------------------|
| Contact switching type | 1 changeover contact |
|------------------------|----------------------|

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

|  |   |
|--|---|
| Type of switch contact                         | Single contact  |
| Contact material                               | AgNi  |
| Maximum switching voltage                      | 250 V AC/DC   |
| Minimum switching voltage                      | 12 V (10 mA)  |
| Limiting continuous current                    | 11 A (see diagram)  |
| Maximum inrush current                         | 24 A (20 ms, N/O contacts)  |
| Min. switching current                         | 10 mA (12 V)  |
| Interrupting rating (ohmic load) max.          | 240 W (24 V DC)<br>62 W (48 V DC)<br>48 W (60 V DC)<br>52 W (110 V DC)<br>66 W (220 V DC)<br>2500 VA (250 V AC) |
| Switching power min.                           | 120 mW  |
| Utilization category CB Scheme (IEC 60947-5-1) | AC15, 3 A/250 V (N/O contact)<br>DC13, 2 A/24 V (N/O contact)   |

## Connection data

|   |   |
|---|---|
| Connection method   | Screw connection  |
| Stripping length  | 8 mm  |
| Conductor cross-section rigid   | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section rigid (2 conductors with same cross section)    | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>   |
| Conductor cross-section flexible  | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup><br>0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> (Ferrule with plastic sleeve)          |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup><br>0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve) |
| Conductor cross-section AWG   | 20 ... 10 (solid)<br>20 ... 12 (flexible)   |
| Tightening torque   | 0.5 Nm ... 0.6 Nm   |

## Dimensions

### Item dimensions

|        |       |
|--------|-------|
| Width  | 16 mm |
| Height | 90 mm |
| Depth  | 75 mm |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V2 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|                                   |                   |
|-----------------------------------|-------------------|
| Degree of protection (Relay base) | IP20 (Relay base) |
|-----------------------------------|-------------------|

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

|   |                  |
|---|------------------|
| Degree of protection (Relay)            | RT II (Relay)    |
| Ambient temperature (operation)         | -40 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

## Standards and regulations

|                       |              |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|-----------------------|--------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

## Drawings

Diagram



- ① DC coils
- ② AC coils


Operating voltage range

Diagram



Interrupting rating

Diagram



Contact derating

2905659

<https://www.phoenixcontact.com/us/products/2905659>

Diagram



Electrical service life

Diagram



Service life reduction factor

2905659

<https://www.phoenixcontact.com/us/products/2905659>



Permissible humidity for operation and storage.

The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^\circ\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^\circ\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^\circ\text{C}$ .

2905659

<https://www.phoenixcontact.com/us/products/2905659>

Circuit diagram



DC coils

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

## Classifications

### ECLASS

ECLASS-13.0

27371601

### ETIM

ETIM 9.0

EC001437

### UNSPSC

UNSPSC 21.0

39122300

# RIF-1-RSC-LDP-24DC/1X21MS - Relay module



2905659

<https://www.phoenixcontact.com/us/products/2905659>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)