

UM-D25SUB/F/M/16DO-RELS/SC049 - Active module



2905752

<https://www.phoenixcontact.com/us/products/2905752>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



16-channel digital output module with spring-cage connection and 25-pos. D-SUB miniature socket strip and 25-pos. D-SUB miniature pin strip, plug-in relay base for fitting 60 V DC or 24 V DC optocouplers, module width: 365 mm

Commercial data

Item number	2905752
Packing unit	1 pc
Minimum order quantity	30 pc
Product key	DK2A92
GTIN	4046356995511
Weight per piece (including packing)	1,257 g
Weight per piece (excluding packing)	1,257 g
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
Utilization restriction	
EMC note	EMC: class A product, see manufacturer's declaration in the download area

Product properties

Product type	Relay Module
Insulation characteristics: Air clearances and creepage distances, input/output	
Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2
Insulation characteristics: Air and creepage distances, output/output	
Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Air clearances and creepage distances, input/output	
Rated insulation voltage	300 V
Rated surge voltage	6 kV (1.2/50 μ s)
Air and creepage distances, output/output	
Rated insulation voltage	300 V
Rated surge voltage	4 kV (1.2/50 μ s)

Input data

Nominal input voltage U_N	24 V
Input voltage range in reference to U_N	0.9 ... 1.1
Typical input current at U_N	1 A (per channel)
Protective circuit	Freewheeling, LED; Freewheeling diode, LED

Output data

Switching	
Contact switching type	Single contact, 1 changeover contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC

2905752

<https://www.phoenixcontact.com/us/products/2905752>

Limiting continuous current	2 A (per channel)
-----------------------------	-------------------

Connection data

Controller level

Connection in acc. with standard	DIN 41652/IEC 60807-2
Connection method	D-SUB-25 male/D-SUB-25 female
Number of positions	25

Field level

Connection method	Spring-cage connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	365 mm
Height	143 mm
Depth	68 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

2905752

<https://www.phoenixcontact.com/us/products/2905752>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com