

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled shielded round cable; connection 1: EDAC/ELCO socket strip (1x 56-position); connection 2: EDAC/ELCO socket strip (1x 56-position); cable length: variable



Commercial data

Item number	2906066
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C492
Product key	DK2281
Weight per piece (excluding packing)	0.1 MGM
Customs tariff number	85444290
Country of origin	DE

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per path	1.5 A

Cable/line

Cable length	variable
--------------	----------

56X0.34 [PVC]

UL AWM Style	2464/1061
Number of positions	56
Shielded	yes
Cable type	56X0.34 [PVC]
Conductor type	Assembled shielded round cable
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor cross-section	56x 0.34 mm ²
Wire diameter incl. insulation	1.3 mm ±0.05 mm
External cable diameter	14.10 mm ±0.5 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 60 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (at 20 °C)
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Color code: Single-core wire

pink-brown-black	X1 (Z) = X2 (Z)
white	X1 (A) = X2 (A)
brown	X1 (B) = X2 (B)
green	X1 (C) = X2 (C)
yellow	X1 (D) = X2 (D)
gray	X1 (E) = X2 (E)
pink	X1 (F) = X2 (F)
blue	X1 (H) = X2 (H)
red	X1 (J) = X2 (J)
black	X1 (K) = X2 (K)
violet	X1 (L) = X2 (L)
gray-pink	X1 (M) = X2 (M)
red-blue	X1 (N) = X2 (N)
white-green	X1 (P) = X2 (P)
brown-green	X1 (R) = X2 (R)
white-yellow	X1 (S) = X2 (S)
yellow-brown	X1 (T) = X2 (T)
white-gray	X1 (U) = X2 (U)
gray-brown	X1 (V) = X2 (V)
white-pink	X1 (W) = X2 (W)
pink-brown	X1 (X) = X2 (X)
white-blue	X1 (a) = X2 (a)
brown-blue	X1 (b) = X2 (b)
white-red	X1 (c) = X2 (c)
brown-red	X1 (d) = X2 (d)
white-black	X1 (e) = X2 (e)
brown-black	X1 (f) = X2 (f)
gray-green	X1 (h) = X2 (h)
yellow-gray	X1 (j) = X2 (j)
pink-green	X1 (k) = X2 (k)
yellow-pink	X1 (l) = X2 (l)
green-blue	X1 (m) = X2 (m)
yellow-blue	X1 (n) = X2 (n)
green-red	X1 (p) = X2 (p)
yellow-red	X1 (r) = X2 (r)
green-black	X1 (s) = X2 (s)
yellow-black	X1 (t) = X2 (t)
gray-blue	X1 (u) = X2 (u)
pink-blue	X1 (v) = X2 (v)
gray-red	X1 (w) = X2 (w)
pink-red	X1 (x) = X2 (x)
gray-black	X1 (y) = X2 (y)

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

pink-black	X1 (z) = X2 (z)
blue-black	X1 (AA) = X2 (AA)
red-black	X1 (BB) = X2 (BB)
white-brown-black	X1 (CC) = X2 (CC)
yellow-green-black	X1 (DD) = X2 (DD)
gray-pink-black	X1 (EE) = X2 (EE)
blue-red-black	X1 (FF) = X2 (FF)
white-green-black	X1 (HH) = X2 (HH)
green-brown-black	X1 (JJ) = X2 (JJ)
white-yellow-black	X1 (KK) = X2 (KK)
yellow-brown-black	X1 (LL) = X2 (LL)
white-gray-black	X1 (MM) = X2 (MM)
gray-brown-black	X1 (NN) = X2 (NN)
white-pink-black	X1 (Y) = X2 (Y)

Connection data

Field level

Connection method	EDAC/ELCO socket strip
Coding	1-1
Number of connections	1
Number of positions	56

Controller level

Connection method	EDAC/ELCO socket strip
Coding	1-1
Number of connections	1
Number of positions	56

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


CABLE-EC56-F-F-0,34-S/... - Cable

2906066

<https://www.phoenixcontact.com/us/products/2906066>

Drawings

Dimensional drawing



CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906066>



EAC

Approval ID: RU*-DE.HB*35.B00385

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Classifications

ECLASS

ECLASS-13.0	27242220
ECLASS-15.0	27242220

ETIM

ETIM 10.0	EC000237
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

CABLE-EC56-F-F-0,34-S/... - Cable



2906066

<https://www.phoenixcontact.com/us/products/2906066>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com