

PACT RCP-4000A-UIRO - Signal conditioner



2906229

<https://www.phoenixcontact.com/us/products/2906229>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Screw connection technology, standard configuration.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2906229 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C444 |
| Product key | CMMA12 |
| GTIN | 4055626047997 |
| Weight per piece (including packing) | 110.5 g |
| Weight per piece (excluding packing) | 110.5 g |
| Customs tariff number | 85437090 |
| Country of origin | DE |

Technical data

Product properties

| | |
|----------------|--------------------------|
| Product type | Signal conditioner |
| Product family | 4-way signal conditioner |

Electrical properties

General

| | |
|----------------|---|
| Accuracy class | 1 |
|----------------|---|

Input data

Signal

| | |
|-------------------------|-----------------|
| Input signal (at 50 Hz) | 100 mV (1000 A) |
|-------------------------|-----------------|

Measurement

| | |
|------------------|---|
| Number of inputs | 1 |
|------------------|---|

Current transformer

| | |
|--------------------------------|--------|
| Primary rated current I_{pn} | 4000 A |
| Accuracy class | 1 |

Measurement

| | |
|----------------------------|---|
| Maximum transmission error | $\leq 0.5\%$ (From the range end value) |
|----------------------------|---|

Output data

Signal

| | |
|---------------------------------|--|
| Configurable/programmable | Yes |
| Voltage output signal | 0 V ... 10 V (via DIP switch) |
| | 2 V ... 10 V (via DIP switch) |
| | 0 V ... 5 V (via DIP switch) |
| | 1 V ... 5 V (via DIP switch) |
| | 0 V ... 10.5 V (can be set via software) |
| Max. voltage output signal | approx. 12.3 V |
| Current output signal | 0 mA ... 20 mA (via DIP switch) |
| | 4 mA ... 20 mA (via DIP switch) |
| | 0 mA ... 10 mA (via DIP switch) |
| | 2 mA ... 10 mA (via DIP switch) |
| | 0 mA ... 21 mA (can be set via software) |
| Max. current output signal | 24.6 mA |
| Load/output load voltage output | $\geq 10\text{ k}\Omega$ |
| Load/output load current output | $\leq 600\ \Omega$ (20 mA) |
| Ripple | $< 20\text{ mV}_{PP}$ |
| | $< 20\text{ mV}_{PP}$ |

2906229

<https://www.phoenixcontact.com/us/products/2906229>

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
| Stripping length | 10 mm |

Measuring transducer side

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 10 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 26 ... 16 |

Material specifications

| | |
|------------------|-----|
| Housing material | PBT |
|------------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
|---------------------------------|------------------|

Approvals

CMIM

| | |
|-------------|----------------|
| Certificate | CMIM-compliant |
|-------------|----------------|

EMC data

Electromagnetic HF field

| | |
|-----------------|-------------------|
| Frequency range | 16 Hz ... 1000 Hz |
|-----------------|-------------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

PACT RCP-4000A-UIRO - Signal conditioner




2906229

<https://www.phoenixcontact.com/us/products/2906229>

Drawings

Block diagram



PACT RCP-4000A-UIRO - Signal conditioner



2906229

<https://www.phoenixcontact.com/us/products/2906229>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906229>



EAC

Approval ID: RU*DE*08.B.01187/19



UL Listed

Approval ID: E123528



cUL Listed

Approval ID: E123528



cUL Listed

Approval ID: E123528



UL Listed

Approval ID: E123528

PACT RCP-4000A-UIRO - Signal conditioner



2906229

<https://www.phoenixcontact.com/us/products/2906229>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210120 |
| ECLASS-15.0 | 27210120 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

2906229

<https://www.phoenixcontact.com/us/products/2906229>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 7b8669ea-ebc4-419d-b33e-242d6ee496e4 |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com