

# PACT RCP-4000A-UIRO-PT - Signal conditioner



2906230

<https://www.phoenixcontact.com/us/products/2906230>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universally configurable 4-way signal conditioner, with switching output and plug-in connection technology for the electrical isolation of analog signals. Configurable via DIP switch or software. Push-in connection technology, order configuration.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2906230       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C444          |
| Product key                          | CMMA12        |
| GTIN                                 | 4055626048130 |
| Weight per piece (including packing) | 61 g          |
| Weight per piece (excluding packing) | 98 g          |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

2906230

<https://www.phoenixcontact.com/us/products/2906230>

## Technical data

### Product properties

|                |                          |
|----------------|--------------------------|
| Product type   | Signal conditioner       |
| Product family | 4-way signal conditioner |

### Electrical properties

#### General

|                |   |
|----------------|---|
| Accuracy class | 1 |
|----------------|---|

### Input data

#### Signal

|                         |                 |
|-------------------------|-----------------|
| Input signal (at 50 Hz) | 100 mV (1000 A) |
|-------------------------|-----------------|

#### Measurement

|                  |   |
|------------------|---|
| Number of inputs | 1 |
|------------------|---|

#### Current transformer

|                                |        |
|--------------------------------|--------|
| Primary rated current $I_{pn}$ | 4000 A |
| Accuracy class                 | 1      |

### Output data

#### Signal

|                                 |  |
|---------------------------------|--|
| Configurable/programmable       | Yes                                      |
| Voltage output signal           | 0 V ... 10 V (via DIP switch)            |
|                                 | 2 V ... 10 V (via DIP switch)            |
|                                 | 0 V ... 5 V (via DIP switch)             |
|                                 | 1 V ... 5 V (via DIP switch)             |
|                                 | 0 V ... 10.5 V (can be set via software) |
| Max. voltage output signal      | approx. 12.3 V                           |
| Current output signal           | 0 mA ... 20 mA (via DIP switch)          |
|                                 | 4 mA ... 20 mA (via DIP switch)          |
|                                 | 0 mA ... 10 mA (via DIP switch)          |
|                                 | 2 mA ... 10 mA (via DIP switch)          |
|                                 | 0 mA ... 21 mA (can be set via software) |
| Max. current output signal      | 24.6 mA                                  |
| Load/output load voltage output | $\geq 10 \text{ k}\Omega$                |
| Load/output load current output | $\leq 600 \Omega$ (20 mA)                |
| Ripple                          | $< 20 \text{ mV}_{PP}$                   |
|                                 | $< 20 \text{ mV}_{PP}$                   |

### Connection data

|                   |                    |
|-------------------|--------------------|
| Connection method | Push-in connection |
|-------------------|--------------------|

# PACT RCP-4000A-UIRO-PT - Signal conditioner



2906230

<https://www.phoenixcontact.com/us/products/2906230>

|                  |       |
|------------------|-------|
| Stripping length | 10 mm |
|------------------|-------|

## Measuring transducer side

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection                          |
| Stripping length                 | 10 mm                                       |
| Screw thread                     | M3  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 26 ... 12                                   |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
|---------------------------------|------------------|

## Approvals

### CMIM

|             |                |
|-------------|----------------|
| Certificate | CMIM-compliant |
|-------------|----------------|

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# PACT RCP-4000A-UIRO-PT - Signal conditioner




2906230

<https://www.phoenixcontact.com/us/products/2906230>

## Drawings

Block diagram



# PACT RCP-4000A-UIRO-PT - Signal conditioner



2906230

<https://www.phoenixcontact.com/us/products/2906230>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906230>



**EAC**

Approval ID: RU\*DE\*08.B.01187/19



**UL Listed**

Approval ID: E123528



**cUL Listed**

Approval ID: E123528

# PACT RCP-4000A-UIRO-PT - Signal conditioner



2906230

<https://www.phoenixcontact.com/us/products/2906230>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27210120 |
| ECLASS-15.0 | 27210120 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

2906230

<https://www.phoenixcontact.com/us/products/2906230>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |  |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)   |
|                                     | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP                                | 6db40315-f913-41b2-b157-87c89c89c3f9                           |

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)