

UM100-PROFIL 200CM - Profile

2906319

<https://www.phoenixcontact.com/us/products/2906319>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile housing and board base, with a constructional width of 100 mm and a fixed length of 200 cm



Figure shows one version

Your advantages

- Easy installation
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts

Commercial data

Item number	2906319
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC13
Product key	ACHDBA
GTIN	4017918277451
Weight per piece (including packing)	955 g
Weight per piece (excluding packing)	955 g
Customs tariff number	39162000
Country of origin	DE

UM100-PROFIL 200CM - Profile

2906319


<https://www.phoenixcontact.com/us/products/2906319>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM100
Ventilation openings present	no

Dimensions

Dimensional drawing	
Depth	21.5 mm
Length	200 cm

External dimensions

Profile width (external)	122.6 mm
--------------------------	----------

Internal dimensions

Profile width (internal)	100 mm
--------------------------	--------

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Profile)	green (RAL 6021)
Material Profile	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 50 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Relative humidity (storage/transport)	95 %

PCB data

Number of PCB holders	2
Thickness of the PCB	1.4 mm ... 1.8 mm

Mounting

Mounting type	Latching with side elements, latching with foot element
---------------	---

UM100-PROFIL 200CM - Profile



2906319

<https://www.phoenixcontact.com/us/products/2906319>

Mounting position	parallel to the DIN rail
-------------------	--------------------------

Packaging specifications

Type of packaging	packed in cardboard
Outer packaging type	Carton


UM100-PROFIL 200CM - Profile

2906319

<https://www.phoenixcontact.com/us/products/2906319>



Drawings



UM100-PROFIL 200CM - Profile



2906319

<https://www.phoenixcontact.com/us/products/2906319>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM100-PROFIL 200CM - Profile



2906319

<https://www.phoenixcontact.com/us/products/2906319>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com