

1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Allen-Bradley® PLC-5 migration board used to convert 1771 I/O and pre-wired 21-position swing arm (1771-WG, 1771-WH, 1771-WHF, or 1771WHFB) to 25-position (female) D-SUB socket.

Your advantages

- Durable PCB designed to easily mount within 1771 chassis
- Terminal connection with locking tab
- Quick cable connection via D-SUB 25 female connector
- Protective PCB terminal shell for double-spring contacts

Commercial data

Item number	2906375
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BZZ
GTIN	4055626365701
Weight per piece (including packing)	577.5 g
Weight per piece (excluding packing)	550 g
Customs tariff number	85366990
Country of origin	US

1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Technical data

Product properties

Product type	Interface module
Number of positions	21

Electrical properties

Nominal voltage U_N	max. 125 V AC/DC
Max. current carrying capacity per branch	2 A

Supported controller: ALLEN-BRADLEY PLC 5

Suitable I/O card	1771-IFE
	1771-IFF
	1771-IFMS
	1771-IAD
	1771-IBD
	1771-ICD
	1771-IGD
	1771-IND
	1771-IND1
	1771-OAD
	1771-OB
	1771-OBDS
	1771-OGD
	1771-OND

Connection data

Terminal connection

Number of positions	21
---------------------	----

Controller level

Connection method	D-SUB-25 female connector
Number of connections	1
Number of positions	25

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	254 mm
Height	143.5 mm
Depth	23.6 mm

1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

1771-CONTACT21/D25F - Interface card




2906375

<https://www.phoenixcontact.com/us/products/2906375>

Drawings

Dimensional drawing




1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Circuit diagram



1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1771-CONTACT21/D25F - Interface card



2906375

<https://www.phoenixcontact.com/us/products/2906375>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5cd0e314-8a1b-4ebd-8441-4980c123e408

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com