

VIP-CAB-FLK20/OE/0,14/20,0M/S - Cable



2906424

<https://www.phoenixcontact.com/us/products/2906424>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled shielded round cable with additional shield connection and one 20-pos. molded socket strip (90° outlet) and an open end. At the open end, the wires are marked 1 to 20 and are fitted with ferrules, cable length: 20 m

Your advantages

- 20-pos.
- 1:1 connection
- Open end at one end

Commercial data

Item number	2906424
Packing unit	1 pc
Minimum order quantity	2 pc
Product key	DK2AH4
GTIN	4055626074825
Weight per piece (including packing)	1,862.9 g
Weight per piece (excluding packing)	1,828 g
Country of origin	DE

2906424

<https://www.phoenixcontact.com/us/products/2906424>

Technical data

Product properties

Product type	System cable
--------------	--------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (DC)	≤ 24 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 0.5 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μs)

Cable/line

Cable length	20 m
UL AWM Style	2464/1061
Number of positions	20
Shielded	yes
Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	20x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	7.70 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)

VIP-CAB-FLK20/OE/0,14/20,0M/S - Cable



2906424

<https://www.phoenixcontact.com/us/products/2906424>

Smallest bending radius, fixed installation	80 mm
Smallest bending radius, movable installation	144 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of $\geq 18x$ outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Connection data

Flat-ribbon cable connector

Connection in acc. with standard	IEC 60603-13
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	20
Exit angle	90 °
Insertion/withdrawal cycles	> 200
Pitch	2.54 mm

Controller level

Connection method	Single wires
Number of positions	20
Note	The wires are marked and fitted with ferrules

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Diagram



Maximum permissible current per path in uncoiled state

VIP-CAB-FLK20/OE/0,14/20,0M/S - Cable



2906424

<https://www.phoenixcontact.com/us/products/2906424>

Classifications

ECLASS

ECLASS-13.0	27242220
-------------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

2906424

<https://www.phoenixcontact.com/us/products/2906424>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com