

# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SCK measuring module for monitoring photovoltaic systems, 4 x current measurement up to 20 A, 1 x digital input, interface to SCK communication module

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2903242       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C447          |
| Product key                          | CMMD11        |
| GTIN                                 | 4046356729697 |
| Weight per piece (including packing) | 253 g         |
| Weight per piece (excluding packing) | 240.5 g       |
| Customs tariff number                | 90303370      |
| Country of origin                    | DE            |

# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Technical data

### Product properties

|                |                              |
|----------------|------------------------------|
| Product type   | Current measuring transducer |
| Product family | SOLARCHECK                   |

### Insulation characteristics

|                  |   |
|------------------|---|
| Pollution degree | 2 |
|------------------|---|

### Electrical properties

|                    |   |
|--------------------|---|
| Protective circuit | Surge protection; 33 V suppressor diode |
|--------------------|---|

### Supply

|                         |   |
|-------------------------|---|
| Supply voltage range    | via the SOLARCHECK communication module |
| Own current consumption | 43 mA (typical)                         |
|                         | 50 mA (maximum)                         |

### Input data

#### Signal: digital

|                          |                          |
|--------------------------|--------------------------|
| Description of the input | Digital input            |
| Available input sources  | floating switch contacts |
| Cable length             | ≤ 30 m                   |

#### Measurement

|                                  |  |
|----------------------------------|--|
| Number of inputs                 | 4  |
| Input current range              | 0 A DC ... 20 A DC (UL: 0 A DC...25 A DC)    |
| Reverse current detection        | -1 A DC ... 0 mA                             |
| LSB: Current                     | 20 mA  |
| Overload capacity                | 5 x I <sub>N</sub>                           |
| Temperature coefficient, typical | 0.02 %/K (T <sub>K20</sub> )                 |
| Maximum transmission error       | ± 1 % (From the measuring range final value) |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |
| Tightening torque                | 0.5 Nm ... 0.6 Nm                           |

### Interfaces

#### Data: Data interface to SCK-C-MODBUS

|                     |                                 |
|---------------------|---------------------------------|
| Transmission length | ≤ 300 m (0.14 mm <sup>2</sup> ) |
|                     | ≤ 500 m (1.5 mm <sup>2</sup> )  |
| Protocols supported | Proprietary                     |

# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Dimensions

### Item dimensions

|        |          |
|--------|----------|
| Width  | 22.5 mm  |
| Height | 102 mm   |
| Depth  | 128.5 mm |

### Circular conductor

|          |        |
|----------|--------|
| Diameter | 9.5 mm |
|----------|--------|

## Environmental and real-life conditions

### Ambient conditions

|   |                         |
|---|-------------------------|
| Degree of protection                    | IP20                    |
| Ambient temperature (operation)         | -20 °C ... 70 °C        |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C        |
| Altitude                                | ≤ 2000 m                |
| Permissible humidity (operation)        | ≤ 95 % (non-condensing) |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UL, USA/Canada

|                |            |
|----------------|------------|
| Identification | 508 Listed |
|----------------|------------|

### UL, USA

|                |                 |
|----------------|-----------------|
| Identification | 1741 Recognized |
|----------------|-----------------|

## EMC data

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Low Voltage Directive         | Conformance with Low Voltage Directive                               |
| Noise immunity                | EN 61000-6-2   |
| Note                          | When being exposed to interference, there may be minimal deviations. |

### Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

## Standards and regulations

|                       |               |
|-----------------------|---------------|
| Standards/regulations | EN 61010-1    |
|                       | EN 61010-2-30 |

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail: 35 mm   |
|               | DIN rail mounting |


# SCK-M-I-4S-20A - PV string monitoring module

2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Drawings

Block diagram



# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903242>



**UL Recognized**

Approval ID: FILE E 325209



**EAC**

Approval ID: RU\*DE.\*08.B.01536/19



**UL Listed**

Approval ID: E140324



**cUL Listed**

Approval ID: E140324



**UL Recognized**

Approval ID: FILE E 325209



**cUL Listed**

Approval ID: E140324



**UL Listed**

Approval ID: E140324

# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27210123 |
| ECLASS-15.0 | 27210123 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002475 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

# SCK-M-I-4S-20A - PV string monitoring module



2903242

<https://www.phoenixcontact.com/us/products/2903242>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 4deac314-7fc0-4609-8bef-085a361d305c |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)