

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Assembled shielded round cable; controller: Emerson Delta V S-Series; connection 1: IDC/FLK socket strip (2x 24-position); connection 2: IDC/FLK socket strip (2x 24-position); cable length: 8 m



Commercial data

| | |
|------------------------|--------------------------------|
| Item number | 2906958 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK221K |
| GTIN | 4055626145105 |
| Customs tariff number | 85444290 |
| Country of origin | DE |

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Insulation characteristics: Air clearances and creepage distances

| | |
|----------------------|-----------------------|
| Insulation | Functional insulation |
| Overvoltage category | II |
| Pollution degree | 2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|-----------------------|
| Operating voltage (AC) | ≤ 25 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A |
| Current (Per path) | ≤ 0.6 A |

Air clearances and creepage distances

| | |
|--------------------------|--------|
| Rated insulation voltage | 63 V |
| Rated surge voltage | 0.6 kV |

Supported controller: EMERSON DeltaV

| | |
|-------------------|-------------|
| Suitable I/O card | SE4053S2B11 |
| | SE4083S2B11 |

Cable/line

| | |
|--------------|-----|
| Cable length | 8 m |
|--------------|-----|

50X0.14 [PVC]

| | |
|---------------------------------|--------------------------------|
| UL AWM Style | 2464/1061 |
| Number of positions | 50 |
| Shielded | yes |
| Cable type | 50X0.14 [PVC] |
| Conductor type | Assembled shielded round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

| | |
|---|--|
| Conductor cross-section | 50x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 11.00 mm ±0.3 mm |
| Outer sheath, material | Semi-rigid PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km (at 20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 114 mm |
| Smallest bending radius, movable installation | 205 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter) |
| Halogen-free | no |
| Flame resistance | IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) UL VW-1 CSA FT-1 |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Cable for one module |

Connection data

Field level

| | |
|----------------------------------|----------------------|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 2 |
| Number of positions | 24 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Controller level

| | |
|----------------------------------|----------------------|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 2 |
| Number of positions | 24 |
| Conductor cross-section AWG | 26 |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Standards and regulations

Air clearances and creepage distances

| | |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|-----------------------|--------------|

Notes

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958


<https://www.phoenixcontact.com/us/products/2906958>

Drawings

Connection diagram

| FLK24 X1 A | FLK24 X3 B | FLK24 X2 C | FLK24 X4 D | Conductor color |
|---------------|---------------|---------------|---------------|-----------------|
| PIN 1 | PIN 1 | | | black |
| PIN 2 | PIN 2 | | | brown |
| PIN 3 | PIN 3 | | | red |
| PIN 4 | PIN 4 | | | orange |
| PIN 5 | PIN 5 | | | yellow |
| PIN 6 | PIN 6 | | | green |
| PIN 7 | PIN 7 | | | blue |
| PIN 8 | PIN 8 | | | violet |
| PIN 9 | PIN 9 | | | gray |
| PIN 10 | PIN 10 | | | white |
| PIN 11 | PIN 11 | | | white-black |
| PIN 12 | PIN 12 | | | white-brown |
| PIN 13 | PIN 13 | | | white-red |
| PIN 14 | PIN 14 | | | white-orange |
| PIN 15 | PIN 15 | | | white-yellow |
| PIN 16 | PIN 16 | | | white-green |
| PIN 17 | PIN 17 | | | white-blue |
| PIN 18 | PIN 18 | | | white-violet |
| PIN 19 | PIN 19 | | | white-gray |
| PIN 20 | PIN 20 | | | brown-black |
| PIN 21 | PIN 21 | | | brown-red |
| PIN 22 | PIN 22 | | | brown-orange |
| PIN 23 | PIN 23 | | | brown-yellow |
| PIN 24 | PIN 24 | | | brown-green |
| | | PIN 1 | PIN 1 | brown-blue |
| | | PIN 2 | PIN 2 | brown-violet |
| | | PIN 3 | PIN 3 | brown-gray |
| | | PIN 4 | PIN 4 | brown-white |
| | | PIN 5 | PIN 5 | green-black |
| | | PIN 6 | PIN 6 | green-brown |
| | | PIN 7 | PIN 7 | green-red |
| | | PIN 8 | PIN 8 | green-orange |
| | | PIN 9 | PIN 9 | green-blue |
| | | PIN 10 | PIN 10 | green-violet |
| | | PIN 11 | PIN 11 | green-gray |
| | | PIN 12 | PIN 12 | green-white |
| | | PIN 13 | PIN 13 | yellow-black |
| | | PIN 14 | PIN 14 | yellow-brown |
| | | PIN 15 | PIN 15 | yellow-red |
| | | PIN 16 | PIN 16 | yellow-orange |
| | | PIN 17 | PIN 17 | yellow-blue |
| | | PIN 18 | PIN 18 | yellow-violet |
| | | PIN 19 | PIN 19 | yellow-gray |
| | | PIN 20 | PIN 20 | yellow-white |
| | | PIN 21 | PIN 21 | gray-black |
| | | PIN 22 | PIN 22 | gray-brown |
| | | PIN 23 | PIN 23 | gray-red |
| | | PIN 24 | PIN 24 | gray-orange |

Diagram



Maximum permissible current per path in uncoiled state

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121620 |
|-------------|----------|

CABLE-2FLK24/2FLK24/DV/ 8,0M/S - Cable



2906958

<https://www.phoenixcontact.com/us/products/2906958>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com