

# UM-2D25SUB/M/DI - Input module



2907013

<https://www.phoenixcontact.com/us/products/2907013>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital VARIOFACE input module, with COMBICON screw connection and two 25-pos. D-SUB pin strips for ABB S 800 I/O modules.

## Commercial data

Item number	2907013
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK2A82
GTIN	4055626156088
Weight per piece (including packing)	318 g
Weight per piece (excluding packing)	318 g
Country of origin	DE

# UM-2D25SUB/M/DI - Input module



2907013

<https://www.phoenixcontact.com/us/products/2907013>

## Technical data

### Product properties

Product type	Interface module
--------------	------------------

#### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Nominal voltage $U_N$	25 V AC/DC
Max. current carrying capacity per branch	1 A
Max. total current of all branches	2.5 A

#### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 $\mu$ s)

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Number of positions	52
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	D-SUB pin strip
Number of connections	2
Number of positions	25

### Signaling

Status display	no
Status display present	no

### Dimensions

#### Item dimensions

Width	139 mm
Height	90 mm
Depth	65 mm

### Material specifications

# UM-2D25SUB/M/DI - Input module



2907013

<https://www.phoenixcontact.com/us/products/2907013>

Color	green (RAL 6021)
Housing insulation material	PVC

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# UM-2D25SUB/M/DI - Input module

2907013

<https://www.phoenixcontact.com/us/products/2907013>



## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UM-2D25SUB/M/DI - Input module



2907013

<https://www.phoenixcontact.com/us/products/2907013>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)