

ECOR-1-BSC3/2X21 - Relay base

2907518

<https://www.phoenixcontact.com/us/products/2907518>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ECOR-1... relay base, for miniature power relay or miniature switching relay with 1 or 2 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Commercial data

Item number	2907518
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C463
Product key	DKF312
GTIN	4055626214351
Weight per piece (including packing)	50.86 g
Weight per piece (excluding packing)	49.44 g
Customs tariff number	85366990
Country of origin	CN

ECOR-1-BSC3/2X21 - Relay base



2907518

<https://www.phoenixcontact.com/us/products/2907518>

Technical data

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition

Electrical properties

Nominal voltage U_N	250 V AC/DC
Nominal current I_N	12 A

Connection data

Input side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section flexible	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Tightening torque	0.5 Nm ... 0.7 Nm

Output side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Conductor cross-section flexible	2x 0.2 mm ² ... 2.5 mm ² (without ferrule)
	2x 0.2 mm ² ... 1.5 mm ² (with ferrule)
Tightening torque	0.5 Nm ... 0.7 Nm

Dimensions

Item dimensions

Width	15.7 mm
Height	79.2 mm
Depth (Retaining bracket)	69 mm (ECOR-RH-1L)
	78 mm (ECOR-RH-1H)

Drill hole

Diameter	3.3 mm
----------	--------

Material specifications

Color	traffic gray B (RAL 7043)
-------	---------------------------

ECOR-1-BSC3/2X21 - Relay base



2907518

<https://www.phoenixcontact.com/us/products/2907518>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Mounting

Mounting type	DIN rail mounting
Mounting position	any

ECOR-1-BSC3/2X21 - Relay base



2907518

<https://www.phoenixcontact.com/us/products/2907518>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907518>



cUL Recognized
Approval ID: FILE E 113228



UL Recognized
Approval ID: FILE E 113228



EAC
Approval ID: RU C-DE.**08.B.01419



cULus Recognized
Approval ID: E113228

ECOR-1-BSC3/2X21 - Relay base



2907518

<https://www.phoenixcontact.com/us/products/2907518>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 10.0	EC001456
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-1-BSC3/2X21 - Relay base



2907518

<https://www.phoenixcontact.com/us/products/2907518>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.869 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com