# TTC-6P-1X2-12DC-I-P - Surge protection plug

2907839

https://www.phoenixcontact.com/us/products/2907839

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

600 mA IEC

12 V IEC



Surge protection plug with integrated status indicator on the module for a 2-wire floating signal circuit. Nominal voltage: 12 V DC

## Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Continuous monitoring of protective devices, plus mechanical status indicator with optional remote signaling
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features
- Easy testing and documentation with CHECKMASTER 2 with pluggable protective modules
- The signal is not influenced during maintenance work, thanks to the impedance-neutral insertion and removal of protective plugs

ELEKTROGERÄTE RÜCKNAHME

## Commercial data

| | |
|---|---|
| Item number | 2907839 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | CL02 |
| Product key | CL216Z |

| | |
|---|---|
| GTIN | 4055626633473 |
| Weight per piece (including packing) | 15.5 g |
| Weight per piece (excluding packing) | 15.5 g |
| Customs tariff number | 85363010 |
| Country of origin | DE |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Replacement plug |
| Product family | TERMITRAB complete |
| Type | Male |

Insulation characteristics

| | |
|---|---|
| Overvoltage category | III |
| Pollution degree | 2 |


### Electrical properties

| | |
|---|---|
| Nominal voltage $U_N$ | 12 V DC |

### Connection data

| | |
|---|---|
| Connection method | pluggable |

### Dimensions

| | |
|---|---|
| Dimensional drawing |   |
| Width | 6.2 mm +0.1 mm |
| Height | 39 mm |
| Depth | 60.3 mm |

### Material specifications

| | |
|---|---|
| Color | light gray (RAL 7035) |
| | gray (RAL 7042) |
| Flammability rating according to UL 94 | V-0 |
| Insulating material | PBT |
| Housing material | PBT |

### Protective circuit

| | |
|---|---|
| Nominal voltage $U_N$ | 12 V DC |
| Maximum continuous operating voltage $U_C$ | 15 V DC |
| Rated current | 600 mA (56 °C) |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

| | |
|---|---|
| Altitude | ≤ 4000 m (amsl) |
| Permissible humidity (operation) | 5 % ... 95 % |

## Standards and regulations

EN 61643-21


| | |
|---|---|
| Standards/specifications | EN 61643-21 |
| Note | 2001 + A1:2009 + A2:2013 |
| Standards/specifications | IEC 61643-21 |
| Note | 2000 + corrigendum 2001 + A1:2008, modified + A2:2012 |

## Mounting


| | |
|---|---|
| Mounting type | on base element |

## Drawings

Dimensional drawing




Circuit diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2907839

**CSA**
Approval ID: 70136717

**DNV GL**
Approval ID: TAE000027G

**UL Listed**
Approval ID: FILE E 138168

**CSAus**
Approval ID: 70136717

**UAE-RoHS**
Approval ID: 22-06-16192

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27171501 |
| ECLASS-15.0 | 27171501 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001466 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121600 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a) |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 0531cee1-b7d1-440c-894c-beabda9a1171 |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com