BRIDGE-PT 6 - Bridge

2904494

https://www.phoenixcontact.com/us/products/2904494

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



3-phase loop bridge for 6 CONTACTRON modules, with Push-in connection and 22.5 mm housing width, connecting cable: 3 m

Your advantages

- Bridging of 2 to 10 devices with maximum module spacing of 22.5 mm
- Considerable reduction in wiring
- Up to 575 V AC/3 x 25 A

Commercial data

Item number	2904494
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C470
Product key	DK74Z1
GTIN	4046356845298
Weight per piece (including packing)	376 g
Weight per piece (excluding packing)	350.5 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Product type	Loop bridge
Product family	CONTACTRON
Number of bridgeable modules	6

Electrical properties

Operating voltage range	42 V AC ... 575 V AC
Operating current	≤ 25 A

Material specifications

Color	gray (RAL 7042)

Cable/line

Connecting cable length	3 m
Cable cross section	2.5 mm²

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/2904494

UL Listed
Approval ID: FILE E 172140

cUL Listed
Approval ID: FILE E 172140

cUL Listed
Approval ID: E228652

UL Listed
Approval ID: E228652

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886

UNSPSC

UNSPSC 21.0	39121100

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com