

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cast front adapter with attached, halogen-free round cable and a 40-pos. socket strip injection-molded on both sides for the connection of Yokogawa controllers. Cable length: 35.0 m

Your advantages

- Molded connectors
- Can be screwed on
- KS/AKB-compatible connectors on the module side
- Lateral cable outlet of the I/O module

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2904650 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C421 |
| Product key | DK222N |
| GTIN | 4046356868297 |
| Weight per piece (including packing) | 5,734 g |
| Weight per piece (excluding packing) | 5,393 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Front adapter |
|--------------|---------------|

Electrical properties

| | |
|------------------------|-----------------------|
| Operating voltage (DC) | ≤ 30 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path) | ≤ 500 mA (uncoiled) |

Supported controller: YOKOGAWA CS3000 CentumVP

| | |
|-------------------|--------|
| Suitable I/O card | AAI543 |
| | AAI141 |
| | AAI143 |
| | AAI835 |
| | AAI841 |
| | AAI135 |
| | AAR181 |
| | AAT141 |
| | AAV141 |
| | AAV142 |
| | AAB841 |
| | AAV542 |

Supported controller: YOKOGAWA STARDOM

| | |
|-------------------|---------|
| Suitable I/O card | NFAI543 |
| | NFAI141 |
| | NFAI143 |
| | NFAI835 |
| | NFAI841 |
| | NFAI135 |
| | NFAV141 |
| | NFAV142 |
| | NFAB841 |
| | NFAV542 |

Supported controller: YOKOGAWA ProSafe-RS

| | |
|-------------------|--------|
| Suitable I/O card | SAI143 |
| | SAV144 |
| | SAI533 |

Connection data

Connection 1

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
|----------------------------------|------------------------------|

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

| | |
|-----------------------------|--------------------------------|
| Connection method | Yokogawa, I/O cards compatible |
| Number of connections | 1 |
| Number of positions | 40 |
| Tightening torque | 0.5 Nm (Screw connection) |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Connection 2

| | |
|----------------------------------|------------------------------|
| Connection in acc. with standard | IEC 60603-13 (in compliance) |
| Connection method | Yokogawa, KS compatible |
| Number of connections | 1 |
| Number of positions | 40 |
| Tightening torque | 0.5 Nm (Screw connection) |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Dimensions

Cable

| | |
|--------|------|
| Length | 35 m |
|--------|------|

Cable/line

| | |
|---|---|
| UL AWM Style | 21946 |
| Number of positions | 40 |
| Shielded | yes |
| Conductor type | Assembled, shielded, halogen-free round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 40x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 9.80 mm ±0.4 mm |
| Outer sheath, material | Halogen-free sheath |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 145 Ω/km |
| Insulation resistance | ≥ 20 MΩ*km |
| Smallest bending radius, fixed installation | 102 mm |
| Smallest bending radius, movable installation | 184 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 |
| Halogen-free | yes |
| Flame resistance | IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable) |
| Resistance to oil | can withstand occasional splashes (raw cable) |

2904650

<https://www.phoenixcontact.com/us/products/2904650>

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP20 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Approvals

UKCA

| | |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

Mounting

| | |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Drawings

Connection diagram

| 40-pos. connector the I/O card | 40-pos. connector to the module | Wire color |
|--------------------------------------|---------------------------------------|---------------|
| 1 | 40 | black |
| 2 | 39 | brown |
| 3 | 38 | red |
| 4 | 37 | orange |
| 5 | 36 | yellow |
| 6 | 35 | green |
| 7 | 34 | blue |
| 8 | 33 | violet |
| 9 | 32 | gray |
| 10 | 31 | white |
| 11 | 30 | white-black |
| 12 | 29 | white-brown |
| 13 | 28 | white-red |
| 14 | 27 | white-orange |
| 15 | 26 | white-yellow |
| 16 | 25 | white-green |
| 17 | 24 | white-blue |
| 18 | 23 | white-violet |
| 19 | 22 | white-gray |
| 20 | 21 | brown-black |
| 21 | 20 | brown-red |
| 22 | 19 | brown-orange |
| 23 | 18 | brown-yellow |
| 24 | 17 | brown-green |
| 25 | 16 | brown-blue |
| 26 | 15 | brown-violet |
| 27 | 14 | brown-gray |
| 28 | 13 | brown-white |
| 29 | 12 | green-black |
| 30 | 11 | green-brown |
| 31 | 10 | green-red |
| 32 | 9 | green-orange |
| 33 | 8 | green-blue |
| 34 | 7 | green-violet |
| 35 | 6 | green-gray |
| 36 | 5 | green-white |
| 37 | 4 | yellow-black |
| 38 | 3 | yellow-brown |
| 39 | 2 | yellow-red |
| 40 | 1 | yellow-orange |

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904650>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: E238705

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 125 V | 0.5 A | - | - |



cUL Listed

Approval ID: E238705

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 125 V | 0.5 A | - | - |

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242292 |
| ECLASS-15.0 | 27242292 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002584 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

FLK 40-PA/EZ-DR/HF/KS/3500/YUC - Front adapter



2904650

<https://www.phoenixcontact.com/us/products/2904650>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com