

TC-2KS50-DI32-2EX-PR-CS - Module carrier



2904676

<https://www.phoenixcontact.com/us/products/2904676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination Carrier for redundantly connecting 16 two-channel MACX Analog Ex i NAMUR signal conditioners to digital input cards of the Yokogawa Centum VP controller, via two KS50 connectors, 50-pos. Suitable for Yokogawa ADV151 and ADV161 cards.

Your advantages

- Mechanically decoupled, passive PCB
- Redundant system connection, 50-pos. (KS/AKB-compatible)
- Simple or redundant supply (decoupled from diode, protected against polarity reversal) and monitoring function implemented via separate DIN rail module
- Robust aluminum profile with integrated DIN rail
- Side parts with integrated end clamps
- Cable sets for signal connection are supplied as standard and do not have to be ordered separately

Commercial data

Item number	2904676
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK271C
GTIN	4046356882262
Weight per piece (including packing)	1,800 g
Weight per piece (excluding packing)	1,800 g
Country of origin	DE

TC-2KS50-DI32-2EX-PR-CS - Module carrier



2904676


<https://www.phoenixcontact.com/us/products/2904676>

Set consists of

TC-C-MAX2-SC-31322122 - Cable set

2904674

<https://www.phoenixcontact.com/us/products/2904674>



Cable set for signal transmission on the Termination Carrier for two-channel modules or modules with double output from the MACX Analog Ex series. Connection of terminal points 3.1 and 3.2 as well as 2.1 and 2.2 (signal transmission) to the signal PCB.

TC-C-PTB3-SC-SET1 - Cable set

2905216

<https://www.phoenixcontact.com/us/products/2905216>



Cable set for TC-MACX-MCR-PTB power and fault signaling module (Item No. 2904673), for use on the Termination Carrier for signal conditioners from the MACX Analog Ex series.

TC-2KS50-DI32-2EX-PR-CS - Module carrier


2904676

<https://www.phoenixcontact.com/us/products/2904676>

ME 17,5 TBUS 1,5/ 5-ST-3,81 GY - DIN rail bus connector

1090049

<https://www.phoenixcontact.com/us/products/1090049>




DIN rail bus connector, color: gray, nominal current: 8 A (parallel contacts), rated voltage (III/2): 125 V, number of positions: 5, product range: TBUS5-17,5..., pitch: 3.81 mm, mounting: DIN rail mounting, locking: without, mounting method: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 5 parallel contacts

ME 6,2 TBUS-2 1,5/5-ST-3,81 GY - DIN rail bus connector

2695439

<https://www.phoenixcontact.com/us/products/2695439>



DIN rail bus connector (TBUS), 5-pos., for bridging the supply voltage, can be snapped onto NS 35/... DIN rail in accordance with EN 60715

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Product properties

Product type	Module carrier
--------------	----------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Basic insulation
------------	------------------

Electrical properties

Max. permissible current	1 A (Signal/channel)
Nominal voltage U_N	< 30 V DC (Per signal/channel)

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV

Supported controller: YOKOGAWA CENTUM VP

Suitable I/O card	ADV151
	ADV161

Supply

Designation	Feed-in module
Note	Supply and error message via 2904673 TC-MACX-MCR-PTB
Fuse	2x 2.5 A on PCB, slow-blow (replaceable)
Input voltage	24 V DC
Input voltage range	19.2 V DC ... 30 V DC
Input current	≤ 2 A
Redundant supply	yes, decoupled from diodes
Polarization and surge protection	Yes
Output name	Switching output
Contact switching type	1 N/C contact (alarm = open)
Maximum switching voltage	50 V DC (0.3 A)
	30 V DC (2 A)
	33 V AC (2 A)

Connection data

Power supply

Connection method	Screw connection
Stripping length	7 mm

TC-2KS50-DI32-2EX-PR-CS - Module carrier



2904676

<https://www.phoenixcontact.com/us/products/2904676>

Number of connections	1
Number of positions	6
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	Yokogawa, KS compatible
Number of connections	2
Number of positions	50

Signaling

Status display	1 x red LED (error) 2x green LEDs (PWR1 and PWR2)
----------------	--

Dimensions

Width	242 mm
Height	170 mm
Depth	159.5 mm

Material specifications

Flammability rating according to UL 94	V0
--	----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Ambient temperature (operation)	-20 °C ... 60 °C (Please observe module specifications)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Shock	15g, according to IEC 60068-2-27
Vibration (operation)	2g, according to IEC 60068-2-6

Approvals

UL, USA/Canada

Identification	UL 61010 Listed Class I, Div. 2, Groups A, B, C, D T4 Class I, Zone 2, Group IIC
----------------	--

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

TC-2KS50-DI32-2EX-PR-CS - Module carrier



2904676

<https://www.phoenixcontact.com/us/products/2904676>

Mounting type	DIN rail mounting
Assembly note	No end clamp
Mounting position	vertical, horizontal

2904676

<https://www.phoenixcontact.com/us/products/2904676>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904676>

 UL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 UL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

TC-2KS50-DI32-2EX-PR-CS - Module carrier



2904676

<https://www.phoenixcontact.com/us/products/2904676>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2904676

<https://www.phoenixcontact.com/us/products/2904676>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	16e09393-8315-4b9f-a74c-6ef1aadee7fc

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com