

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wall-mounted NEMA 4/4X (IP66/67) polycarbonate enclosure with surge protection for 60 V AC/DC power and a divided compartment ready for additional Isolated Loop Protection.

Your advantages

- Eligible for limited lifetime warranty (in some U.S. markets)
- Customizable: expand base unit with SPDs to suit your application
- Polycarbonate and 316L stainless steel enclosures available

Commercial data

Item number	2908681
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL20
Product key	CL1481
GTIN	4055626321455
Weight per piece (including packing)	760 g
Weight per piece (excluding packing)	648 g
Country of origin	DE

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Set consists of

PLT-SEC-T3-60-FM-UT - Type 3 surge protection device

2907917

<https://www.phoenixcontact.com/us/products/2907917>



Type 3 surge protection, consisting of protective plug and base element, with integrated status indicator and remote signaling for single-phase power supply networks. Nominal voltage: 60 V AC/DC

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	------------------------------------------------------------------------------------------------

Product properties

Product type	Device protection
Type	DIN rail module, two-section, divisible
Surge protection fault message	optical
EN type	T2 / T3
Number of ports	One

Electrical properties

Nominal voltage U_N	60 V AC (Power)
-----------------------	-----------------


Indicator/remote signaling

Connection name	Remote fault indicator contact
Switching function	Changeover contact

Connection data

Screw thread	M3
Tightening torque, min	0.5 Nm
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	4 mm ²
Connection method	Screw connection
Screw thread	M3

Dimensions

Dimensional drawing	
Width	130 mm
Height	180 mm
Depth	120 mm

Material specifications

Housing material	PC
------------------	----

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Protective circuit

Power supplies

Direction of action	L/N-PE & Signal Line-Shield-Earth Ground
Nominal voltage U_N	60 V AC (TN-S)

Information technology

Nominal voltage U_N	60 V AC (Power)
Max. operating voltage U_{max}	80 V AC (Power)
Nominal current I_N	20 A (Power)
Max. discharge current I_{max} (8/20) μ s	4 kA (Power)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/NEMA 4X
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	\leq 6000 mm (operating voltage remote contact \leq 150 V)
Permissible humidity (operation)	5 % ... 95 %

Mounting

Mounting type	Panel mounting
---------------	----------------

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Drawings

Dimensional drawing




BXT-4XP-SEC-T3-60-FM - Surge protection device

2908681

<https://www.phoenixcontact.com/us/products/2908681>



Connection diagram



BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908681>



UL Listed

Approval ID: FILE E 330181



cUL Listed

Approval ID: FILE E 330181

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Classifications

ECLASS

ECLASS-13.0	27171203
ECLASS-15.0	27171203

ETIM

ETIM 9.0	EC000942
----------	----------

BXT-4XP-SEC-T3-60-FM - Surge protection device



2908681

<https://www.phoenixcontact.com/us/products/2908681>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
-----------------------------------------	-------------------------------------------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com