

RAD-PIG-RSMA-N-EX/ATEX - Antenna barrier



2904788

<https://www.phoenixcontact.com/us/products/2904788>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna barrier, type of protection: Ex d, Ex mb, Ex i, barrier installation: zone 1, antenna installation: zone 0, 1 or 2, frequency range: 0.3 GHz ... 6 GHz, connection: RSMA (male) -> N (female), incl. 0.7 m / 2.3 ft. connection cable, ATEX and IECEx approval



Your advantages

- Universal use (frequency range of 0.3 ... 6 GHz)
- Use of standard antennas in the hazardous area of zone 0, 1, and 2

Commercial data

Item number	2904788
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6A3
GTIN	4046356889278
Weight per piece (including packing)	215.5 g
Weight per piece (excluding packing)	215.5 g
Customs tariff number	85177000
Country of origin	US

RAD-PIG-RSMA-N-EX/ATEX - Antenna barrier



2904788

<https://www.phoenixcontact.com/us/products/2904788>

Technical data

Product properties

Product type	Coaxial cable
--------------	---------------

Electrical properties

Frequency range	0.3 GHz ... 6 GHz
Impedance	50 Ω
Maximum error voltage U_m	250 V DC
Maximum HF output power P	2 W
Maximum capacity	5.64 nF

Connection data

Connection method	N (female)
Connection method	RSMA (male)

Material specifications

Outer material connection	Stainless steel
---------------------------	-----------------

Cable/line

Cable length	0.76 m
--------------	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

Conformity/Approvals

ATEX	Ⓜ II 2(1)G, Ex d mb [ia] IIC
------	------------------------------

Mounting

Mounting method	Bulkhead, M25 thread
-----------------	----------------------


RAD-PIG-RSMA-N-EX/ATEX - Antenna barrier

2904788


<https://www.phoenixcontact.com/us/products/2904788>

Drawings

Dimensional drawing



Application drawing



RAD-PIG-RSMA-N-EX/ATEX - Antenna barrier



2904788

<https://www.phoenixcontact.com/us/products/2904788>

Classifications

UNSPSC

UNSPSC 21.0	26121606
-------------	----------

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com