

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The output loop-powered head transmitter transmits up to two sensor signals from RTD and TC sensors as well as from resistance-type sensors and voltage sensors via HART communication or 4 ... 20 mA, configurable. SIL 2/3, intrinsic safety.

Commercial data

Item number	2908743
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C430
Product key	DK1242
GTIN	4055626347790
Weight per piece (including packing)	197.1 g
Weight per piece (excluding packing)	197.1 g
Customs tariff number	85437090
Country of origin	DE

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Technical data

Product properties

Product type	Temperature transmitter
Product family	Field Analog

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Electrical isolation between input and output	yes
Step response (0–99%)	0.8 s (TC)

Electrical isolation Input/output

Test voltage	2 kV AC
--------------	---------

Supply

Supply voltage range	loop-powered, no external supply necessary
	11 V ... 42 V (Standard)
	11 V ... 32 V (SIL active)
	11 V ... 30 V (Ex)

Input data

Measurement

Input voltage range	-20 mV ... 100 mV
Sensor types (RTD) that can be used	Pt, Ni, Cu sensors: 2, 3, 4-wire
Sensor types that can be used (TC)	A, B, C, D, E, J, K, L, N, R, S, T, U
Temperature measuring range	-250 °C ... 2500 °C (Range depending on the sensor type)
	-200 °C ... 850 °C (Pt 100)
Temperature measuring range	> 10 K (RTD)
	> 50 K (TC)
Linear resistance measuring range	10 Ω ... 2000 Ω (Minimum measuring span: 10 Ω)

Output data

Signal

Current output signal	4 mA ... 20 mA (HART)
	20 mA ... 4 mA (HART)
Max. current output signal	23 mA
Load	(U _L - 11 V) / 0,023 A
HART coding	FSK ± 0.5 mA
HART version	7
Transmission speed	1200 Baud
Mains frequency filter	50/60 Hz

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Communication resistance	≥ 250 Ω
Switch-on delay	approx. 10 s (HART)
	approx. 28 s (Measured value)

Connection data

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP33 (upon installation in field housing IP66/67, NEMA 4X)
Ambient temperature (operation)	-40 °C ... 85 °C
	-40 °C ... 70 °C (SIL active)
Ambient temperature (storage/transport)	-50 °C ... 100 °C
Altitude	≤ 4000 m (Above sea level)
Climatic class	C1
Permissible humidity (operation)	5 % ... 95 % (condensation permitted)

Approvals

CE

Certificate	CE-compliant
-------------	--------------

ATEX

Identification	⊕ II 1G Ex ia IIC T6...T4 Ga
	⊕ II 2G Ex ia IIC T6...T4 Gb
Certificate	EPS 17 ATEX 1 130 X

IECEX

Identification	Ex ia IIC T6...T4 Ga
	Ex ia IIC T6...T4 Gb
Certificate	IECEX EPS 17.0076X

UL, USA/Canada

Identification	UL 61010 Recognized
----------------	---------------------

FM

Identification	NI / Class I / Div. 1, 2 / Group ABCD T6/T5/T4
	IS / Class I / Div. 1, 2 / Group ABCD

CSA

Identification	Exia / Class I / Group ABCD T6/T5/T4
----------------	--------------------------------------

Mounting

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Assembly note

Installation in connection head according to DIN 43729 form B


FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer

2908743

<https://www.phoenixcontact.com/us/products/2908743>

Drawings

Block diagram



Block diagram for FA MCR-EX-HT-TS-I-OLP-PT

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Classifications

UNSPSC

UNSPSC 21.0	41112105
-------------	----------

FA MCR-EX-HT-TS-I-OLP-PT - Head-mounted transducer



2908743

<https://www.phoenixcontact.com/us/products/2908743>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com