

1771-CARDEGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Allen-Bradley® PLC-5 migration board used to convert 1771 I/O and pre-wired 10-position swing arm (1771-WA or 1771-WC) to 25-position (female) D-SUB socket

Your advantages

- Durable PCB designed to easily mount within 1771 chassis
- Card edge connection with locking tab
- Quick cable connection via D-SUB 25 female connector

Commercial data

Item number	2908756
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BZZ
GTIN	4055626365725
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85366990
Country of origin	US

1771-CARDEDGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Technical data

Product properties

Product type	Interface module
Number of positions	10

Electrical properties

Nominal voltage U_N	max. 125 V AC/DC
Max. current carrying capacity per branch	2 A

Supported controller: ALLEN-BRADLEY PLC 5

Suitable I/O card	1771-AF
	1771-DW
	1771-IA/C
	1771-IA2
	1771-IB
	1771-IC
	1771-IG
	1771-IH
	1771-IN
	1771-IQ
	1771-IT
	1771-IV
	1771-OA
	1771-OB
	1771-OC
	1771-OFE
	1771-OFE1
	1771-OFE2
	1771-OFE3
	1771-OG
1771-ON	
1771-OP	
1771-OX	

Connection data

PCB edge contact

Number of positions	10
---------------------	----

Controller level

Connection method	D-SUB-25 female connector
Number of connections	1
Number of positions	25

1771-CARDEDGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	254 mm
Height	153.2 mm
Depth	21.3 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

1771-CARDEDGE10/D25F - Interface card





2908756

<https://www.phoenixcontact.com/us/products/2908756>

Drawings

Dimensional drawing




1771-CARDEDGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Circuit diagram



1771-CARDEDGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1771-CARDEDGE10/D25F - Interface card



2908756

<https://www.phoenixcontact.com/us/products/2908756>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	31cc8dda-7b0a-4495-b0ea-32bebec6e02c

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com