

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop, safety doors, and light grids up to SIL 3, Cat. 4, PL e, 1 or 2-channel operation, automatic start, 2 enabling current paths (1-channel), $U_S = 24 \text{ V DC}$, fixed screw terminal block

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061
- Low housing width of just 6.8 mm
- 2 channel control
- 2 single-channel enabling current paths
- Automatic activation

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2904958 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN01 |
| Product key | DNA171 |
| GTIN | 4046356904889 |
| Weight per piece (including packing) | 76.4 g |
| Weight per piece (excluding packing) | 68.188 g |
| Customs tariff number | 85371098 |
| Country of origin | DE |

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|----------------|--|
| Product type | Safety relays |
| Product family | PSRmini |
| Application | Emergency stop |
| | Safety door |
| | Light grid |
| | Magnetic switch |
| | Transponder |
| Control | 1 and 2 channel |
| Relay type | Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Times

| | |
|-------------------------------|--|
| Typical response time | < 175 ms |
| Typ. starting time with U_S | < 250 ms (when controlled via A1) |
| Typical release time | < 20 ms (when controlled via A1 or S12 and S22.) |
| Restart time | 1 s (Boot time, after switching on the supply voltage) |
| Recovery time | < 500 ms |

Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 3 W ($U_S = 26.4$ V, $I_L^2 = 36$ A ² , $P_{Total\ max} = 1.2$ W + 1.8 W) |
| Nominal operating mode | 100% operating factor |
| Rated insulation voltage | 250 V AC |
| Rated surge voltage/insulation | See data sheet, section "Insulation coordination". |

Supply

| | |
|--|---|
| Designation | A1/A2 |
| Rated control circuit supply voltage U_S | 20.4 V DC ... 26.4 V DC |
| Rated control circuit supply voltage U_S | 24 V DC -15 % / +10 % |
| Rated control supply current I_S | typ. 40 mA |
| Power consumption at U_S | typ. 0.96 W |
| Inrush current | 4.5 A ($\Delta t < 120$ μ s at U_S) |
| Filter time | 1 ms (at A1 in the event of voltage dips at U_S) |
| Protective circuit | Surge protection; Suppressor diode |
| | Serial protection against polarity reversal |

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Input data

Digital: Sensor circuit (S12, S22)

| | |
|---|---|
| Description of the input | safety-related sensor inputs |
| Input voltage range "0" signal | 0 V DC ... 5 V DC (for safe Off; at S12 and S22) |
| Input voltage range "1" signal | 20.4 V DC ... 26.4 V DC |
| Input current range "0" signal | 0 mA ... 2 mA (for safe Off; at S12 and S22) |
| Inrush current | < 20 mA (typ. with U_S) |
| Filter time | max. 1.5 ms (Test pulse width of low test pulses) Test pulse rate = 5 x Test pulse width |
| Concurrency | ∞ |
| Max. permissible overall conductor resistance | 150 Ω |
| Protective circuit | Suppressor diode |
| Voltage at input/start and feedback circuit | 24 V DC -15 % / +10 % |
| Current consumption | < 5 mA (with U_S/I_x to S12) < 5 mA (with U_S/I_x to S22) |

Output data

Relay: Enabling current path (13/14, 23/24)

| | |
|-----------------------------|--|
| Output description | safety-related N/O contacts (1-channel) |
| Number of outputs | 2 (undelayed) |
| Contact switching type | 2 enabling current paths |
| Contact material | AgSnO ₂ |
| Switching voltage | min. 12 V AC/DC max. 250 V AC/DC |
| Switching power | min. 60 mW |
| Inrush current | min. 3 mA max. 6 A |
| Switching capacity | 2 A (AC15) 4 A (DC13) |
| Limiting continuous current | max. 6 A |
| Sq. Total current | 72 A ² (observe derating) |
| Switching frequency | max. 0.1 Hz |
| Mechanical service life | 10x 10 ⁶ cycles |
| Output fuse | 6 A gL/gG (N/O contact) 4 A gL/gG (for low-demand applications) |

Connection data

Connection technology

| | |
|-----------|----|
| pluggable | no |
|-----------|----|

Conductor connection

| | |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

| | |
|----------------------------------|---|
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 26 ... 12 |
| Stripping length | 12 mm |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Signaling

| | |
|---------------------------|-----------------|
| Status display | 2 x LED (green) |
| Operating voltage display | 1 x LED (green) |

Dimensions

| | |
|--------|----------|
| Width | 6.8 mm |
| Height | 93.1 mm |
| Depth | 102.5 mm |

Material specifications

| | |
|------------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | PBT |

Characteristics

Safety data

| | |
|----------------------------|---|
| Stop category (EN 60204-1) | 0 |
|----------------------------|---|

Safety data: EN ISO 13849

| | |
|------------------------|--|
| Performance level (PL) | e (4 A DC13; 2 A AC15; 8760 switching cycles/year) |
|------------------------|--|

Safety data: IEC 61508 - High demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: IEC 61508 - Low demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: EN IEC 62061

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Min. degree of protection of inst. location | IP54 |
| Ambient temperature (operation) | -40 °C ... 55 °C (observe derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Maximum altitude | ≤ 2000 m (Above sea level) |
| Max. permissible humidity (storage/transport) | 75 % (on average, 85% infrequently, non-condensing) |
| Max. permissible relative humidity (operation) | 75 % (on average, 85% infrequently, non-condensing) |

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

| | |
|-----------------------|----------------------|
| Shock | 15g |
| Vibration (operation) | 10 Hz ... 150 Hz, 2g |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

Mounting

| | |
|-------------------|------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | See derating curve |
| Mounting position | vertical or horizontal |


PSR-MS60-2NO-24DC-SC - Safety relays

2904958


<https://www.phoenixcontact.com/us/products/2904958>

Drawings

Application drawing



Block diagram



Block diagram


PSR-MS60-2NO-24DC-SC - Safety relays

2904958

<https://www.phoenixcontact.com/us/products/2904958>

Block diagram

PSR-MS60



Key:

- 1 = Voltage limitation
- 2 = Channel 1
- 3 = Control circuit channel 1
- 4 = Start channel 1 and 2
- 5 = Control circuit channel 2
- K1, K2 = Force-guided elementary relays

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904958>



Functional Safety

Approval ID: 44 205 13755202



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 44 780 13755207

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Classifications

ECLASS

| | |
|-------------------|----------|
| ECLASS-13.0 | 27371819 |
| ECLASS-15.0 | 27371819 |
| ECLASS-15.0 ASSET | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001449 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

PSR-MS60-2NO-24DC-SC - Safety relays



2904958

<https://www.phoenixcontact.com/us/products/2904958>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 56d78635-8cd2-4cb8-8997-bfc8194eeaff |

EF3.1 Climate Change

| | |
|---------|----------------|
| CO2e kg | 11.556 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com