

# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version with a screw connection

Measuring transducer repeater power supply and input signal conditioner, HART-transparent. Transmits supplied or active 4...20 mA electrically isolated signals from the field to two loads. 4-way electrical isolation, PLd. Replacement part: 2924838 MACX MCR-SL-RPSSI-2I-SP.

## Commercial data

Item number	2904962
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C401
Product key	DK1111
GTIN	4046356904544
Weight per piece (including packing)	196.08 g
Weight per piece (excluding packing)	196.08 g
Customs tariff number	85437090
Country of origin	DE

# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

## Technical data

### Product properties

Product type	Repeater power supply
No. of channels	1

### Electrical properties

Electrical isolation between input and output	yes
Step response (10-90%)	1.3 ms (for jump 4 mA ... 20 mA, typical)
Maximum temperature coefficient	< 0.01 %/K
Maximum transmission error	< 0.1 % (of final value)
Transmission error, typical	< 0.05 % (of final value)

### Electrical isolation Input/output/power supply

Rated insulation voltage	300 V <sub>rms</sub>
Test voltage	2.5 kV AC (50 Hz, 60 s)
Overvoltage category	II
Degree of pollution	2
Insulation	Safe isolation in accordance with IEC/EN 61010-1

### Electrical isolation Output 1/output 2

Test voltage	1.5 kV AC (50 Hz, 60 s)
--------------	-------------------------

### Supply

Designation	Repeater power supply operation
Nominal supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (24 V DC, -20 % ... +25 %)
Max. current consumption	< 75 mA (24 V DC)
Power dissipation	< 1.45 W (24 V DC/20 mA)

### Supply

Designation	Signal conditioner operation
Nominal supply voltage range	19.2 V DC ... 30 V DC (24 V DC, -20 % ... +25 %)
Max. current consumption	< 46 mA (24 V DC / 20 mA)
Power dissipation	< 1.2 W (24 V DC/20 mA)

## Input data

### Signal: Repeater power supply operation

Description of the input	Repeater power supply operation
Number of inputs	1
Current input signal	4 mA ... 20 mA
Transmitter supply voltage	> 21.5 V (20 mA) > 21 V (23 mA)

### Signal: Signal conditioner operation

# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

Description of the input	Signal conditioner operation
Current input signal	4 mA ... 20 mA
Voltage drop	< 3.9 V (in input isolating amplifier operation)

## Output data

Signal: Repeater power supply operation

Output description	Repeater power supply operation
Number of outputs	2
Current output signal	4 mA ... 20 mA (active)
Load/output load current output	< 450 Ω (20 mA) < 380 Ω (23 mA)
Output ripple	< 20 mV <sub>rms</sub>
Output behavior in the event of an error	0 mA (Cable break in the input) ≥ 23 mA (Cable short-circuit in the input)

Signal: Signal conditioner operation

Output description	Signal conditioner operation
Current output signal	4 mA ... 20 mA (active)
Load/output load current output	< 450 Ω (20 mA) < 380 Ω (23 mA)
Output ripple	< 20 mV <sub>rms</sub>
Output behavior in the event of an error	0 mA (Cable break in the input) ≥ 23 mA (Cable short-circuit in the input)

## Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Interfaces

Data communication (bypass)

HART function	Yes
Protocols supported	HART-transparent

## Signaling

Status display	Green LED (PWR supply voltage)
----------------	--------------------------------

## Dimensions

Width	12.5 mm
Height	99 mm
Depth	114.5 mm

# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

## Material specifications

Color	yellow (RAL 1018)
Flammability rating according to UL 94 (Housing)	V0 (Housing)
Housing material	PA 6.6-FR

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (not assessed by UL)
Ambient temperature (operation)	-20 °C ... 60 °C (Any mounting position)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
Note	and EN 61326

### ATEX

Identification	Ⓜ II 3 G Ex nA IIC T4 Gc X
----------------	----------------------------

### UL, USA/Canada

Identification	UL 61010 Listed
	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, Group IIC T4

### Shipbuilding approval

Identification	C, EMC2
Certificate	DNV GL 11 564-14HH

### Safety Integrity Level (SIL, IEC 61508)

Identification	2
----------------	---

### Performance Level (ISO 13849)

Identification	d
----------------	---

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Noise immunity	EN 61000-6-2
Note	When being exposed to interference, there may be minimal deviations.

### Electromagnetic HF field

Designation	Electromagnetic RF field
Standards/regulations	EN 61000-4-3
Typical deviation from the measuring range final value	3 %

# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

## Fast transients (burst)

Designation	Fast transients (burst)
Standards/regulations	EN 61000-4-4
Typical deviation from the measuring range final value	3 %

## Conducted interference

Designation	Conducted interferences
Standards/regulations	EN 61000-4-6
Typical deviation from the measuring range final value	3 %

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------


# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

## Drawings



# MACX PL-RPSSI-2I-SP - Repeater power supply



2904962

<https://www.phoenixcontact.com/us/products/2904962>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)