

TC-D37SUB-ADIO16-EX-A-RUSIO - Module carrier



2904967

<https://www.phoenixcontact.com/us/products/2904967>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Termination Carrier for connecting 16 MACX Analog Ex i signal conditioners to the Honeywell Remote Universal Safe IO System via D-SUB connector, 37-pos. Suitable for the Honeywell card FC-RUSIO-3224.

Commercial data

Item number	2904967
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK2715
GTIN	4046356916233
Weight per piece (including packing)	333.33 g
Weight per piece (excluding packing)	333.33 g
Country of origin	DE

Technical data

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Module carrier
--------------	----------------

Electrical properties

Supported controller: HONEYWELL RUSIO

Suitable I/O card	FC-RUSIO-3224
-------------------	---------------

Connection data

Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
----------------------	------

Approvals

UL, USA/Canada

Identification	UL 61010 Listed
	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, Group IIC

Mounting


Mounting type	DIN rail mounting
---------------	-------------------


2904967


<https://www.phoenixcontact.com/us/products/2904967>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2904967>

 UL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E330267				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 cUL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

 UL Listed Approval ID: E199827				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	50 V	1 A	-	-

2904967

<https://www.phoenixcontact.com/us/products/2904967>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2904967

<https://www.phoenixcontact.com/us/products/2904967>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	da4d7b9d-235a-4f54-bcb7-e98110de5aa3

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com