


# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-NAMUR signal conditioner for operating proximity sensors and switches. The signals are transmitted to the control level via 1 transistor output (passive). Standard configuration, 3-way isolation, Line fault detection, Safety Integrity Level (SIL, IEC 61508): 3, Screw connection

## Commercial data

Item number	2908807
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C430
Product key	DK1223
GTIN	4055626357553
Weight per piece (including packing)	121.8 g
Weight per piece (excluding packing)	121.8 g
Customs tariff number	85365019
Country of origin	DE

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Technical data

### Product properties

Product type	Isolating switch amplifier
Product family	MINI Analog Pro
Configuration	DIP switches

### System properties

#### Functionality

Configuration	DIP switches
---------------	--------------

### Electrical properties

Electrical isolation	3-way isolation
Electrical isolation between input and output	yes
Line monitoring	Line fault detection

#### Electrical isolation

Overvoltage category	II ( $\leq 5000$ m)
Pollution degree	2 ( $\leq 5000$ m)

#### Electrical isolation Input/output/power supply IEC/EN 61010-1

Standards/regulations	IEC/EN 61010-1
Rated insulation voltage	300 V <sub>rms</sub>
Test voltage	2.5 kV AC (50 Hz, 60 s)
Insulation	Double/reinforced insulation

#### Electrical isolation Input/output/power supply IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	265 V <sub>rms</sub>

#### Electrical isolation Input/output/power supply IEC/EN 60079-7

Standards/regulations	IEC/EN 60079-7
Rated insulation voltage	251 V <sub>rms</sub>

#### Supply

Nominal supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (24 V DC, -20 % ... +25 %)
Power consumption	$\leq 650$ mW

### Input data

#### Signal: NAMUR

Number of inputs	1
Available input sources	NAMUR proximity sensors (IEC/EN 60947-5-6)
	floating switch contacts
	Switch contacts with resistance circuit

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Output data

Switching: Transistor

Output description	passive
Max. switching current	50 mA
Switching frequency	≤ 10 kHz ( $I_{OUT} \geq 5$ mA) ≤ 20 kHz ( $I_{OUT} \geq 30$ mA (further information in the data sheet))

## Connection data

Connection method	Screw connection
Stripping length	10 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (with ferrule) 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (without ferrule)
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12 (flexible)
Tightening torque	0.5 Nm ... 0.6 Nm

## Ex data

Ex installation (EPL)	Gc
	Div. 2
Ex i circuits (EPL)	[Ga]
	[Da]
	[Ma]
	[Div. 1]

## Safety data

Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Max. output voltage $U_o$	10.1 V
Max. output current $I_o$	10.9 mA
Max. output power $P_o$	28 mW
Safety-related maximum voltage $U_m$	253 V AC (≤ 2000 m)
	125 V DC (≤ 2000 m)
	121 V AC (> 2000 m ... 3000 m)
	110 V DC (> 2000 m ... 3000 m)
	33 V AC/DC (> 3000 m ... 4000 m)
	33 V AC/DC (> 4000 m ... 5000 m)
IIA (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	300 mH / 93 μF
IIB/IIIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 19.4 μF
IIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	300 mH / 2.87 μF

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

I (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	300 mH / 160 $\mu$ F
IIB/IIA (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 1 $\mu$ F
IIIC (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 1 $\mu$ F
IIC (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 500 nF, 50 mH / 570 nF, 5 mH / 590 nF, 1 mH / 590 nF, 10 $\mu$ H / 590 nF
I/IIIB/IIA/IIIC (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 1 $\mu$ F, 5 mH / 1 $\mu$ F, 1 mH / 1 $\mu$ F, 10 $\mu$ H / 1 $\mu$ F
I (mixed circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	100 mH / 1 $\mu$ F

## Signaling

Status display	Green LED (supply voltage)
	Yellow LED (switching state / status, lights up when output circuit is active)
	Red LED (line errors)

## Dimensions

Width	6.2 mm
Height	109.81 mm
Depth	119.2 mm

## Material specifications

Color	gray (RAL 7042)
Housing material	PBT

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

### Altitude range (IEC/EN 61010-1)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Rated insulation voltage	300 $V_{rms}$ (Input/output/power supply)
Insulation	Double/reinforced insulation

### Altitude range (IEC/EN 61010-1)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Rated insulation voltage	300 $V_{rms}$ (Input/output/power supply)
Insulation	Double/reinforced insulation

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Altitude range (IEC/EN 61010-1)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Rated insulation voltage	150 V <sub>rms</sub> (Input/output/power supply)
Insulation	Double/reinforced insulation

## Altitude range (IEC/EN 60079-11)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Rated insulation voltage	150 V <sub>rms</sub> (Input/output/power supply)

## Altitude range (IEC/EN 60079-11)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Rated insulation voltage	60 V <sub>rms</sub> (Input/output/power supply)

## Altitude range (IEC/EN 60079-11)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Rated insulation voltage	60 V <sub>rms</sub> (Input/output/power supply)

## Altitude range (IEC/EN 60079-7)

Height range	> 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 63 °C
Rated insulation voltage	162 V <sub>rms</sub> (Input/output/power supply)

## Altitude range (IEC/EN 60079-7)

Height range	> 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 56 °C
Rated insulation voltage	60 V <sub>rms</sub> (Input/output/power supply)

## Altitude range (IEC/EN 60079-7)

Height range	> 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 49 °C
Rated insulation voltage	60 V <sub>rms</sub> (Input/output/power supply)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3 (1) G Ex ec [ia Ga] IIC T4 Gc
	⊕ I (M1) [Ex ia Ma] I
Certificate	IBExU 21 ATEX 1061 X

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## IECEX

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
	[Ex ia Ma] I
Certificate	IECEX IBE 21.0022 X

## CCC / China-Ex

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
Certificate	2023122316116235

## UL, USA/Canada

Identification	UL 61010-2-201 Listed
	Class I, Div. 1, Groups A, B, C, D
	Class II, Div. 1, Groups E, F, G
	Class III, Div. 1
	Class I, Zone 0, 1, 2, Groups IIC, IIB, IIA
	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2
	AEx ec [ia Ga] IIC T4 Gc; AEx ec [ia IIIC Da] IIC T4 Gc
	Ex ec [ia Ga] IIC T4 Gc X; Ex ec [ia IIIC Da] IIC T4 Gc X
	Class I, Zone 0, [AEx ia Ga] IIC, [Ex ia Ga] IIC X
Class I, Zone 20, [AEx ia Da] IIIC, [Ex ia Da] IIIC X	
Certificate	UL C.D.-No 097285872

## Shipbuilding approval

Certificate	DNV TAA00003FZ
-------------	----------------

## Safety Integrity Level (SIL, IEC 61508)

Identification	3
----------------	---

## INMETRO

Identification	[Ex ia Ma] I
	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec [ia Ga] IIC T4 Gc
Certificate	DNV 23.0188 X

## Shipbuilding data

Temperature	B
Humidity	B
Vibration	A
EMC	A
Enclosure	Required protection according to the Rules shall be provided

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

	upon installation on board
--	----------------------------

## EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
Noise immunity	EN 61000-6-2
Noise immunity	EN 61326-3-2

## Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

## Standards and regulations

Electrical isolation	3-way isolation
----------------------	-----------------

## GB Standard

Standards/regulations	GB/T 3836.1
	GB/T 3836.3
	GB/T 3836.4

## Mounting

Mounting type	DIN rail mounting
Mounting position	any


# MINI MCR-EX-NAM-T - Isolation switch amplifier

2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Drawings

Block diagram



# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908807>



**cULus Listed**

Approval ID: E238705



**Functional Safety**

Approval ID: 1435.IM.131623/19

**DNV**

Approval ID: TAA00003FZ



**cULus Listed**

Approval ID: E238705



**IECEx**

Approval ID: IECEx IBE 21.0022X



**ATEX**

Approval ID: IBExU21ATEX1061 X



**CCC**

Approval ID: 2023122316116235

**INMETRO**

Approval ID: DNV 23.0188 X



**cULus Listed**

Approval ID: E196811



**cULus Listed**

Approval ID: E196811

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Classifications

### ECLASS

ECLASS-13.0	27210121
ECLASS-15.0	27210121
ECLASS-15.0 ASSET	27250101

### ETIM

ETIM 10.0	EC001485
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# MINI MCR-EX-NAM-T - Isolation switch amplifier



2908807

<https://www.phoenixcontact.com/us/products/2908807>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	4ea9b9f3-7b40-4a82-9577-ff161d12836c

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)