

# FLX-D37F/32CH/DO/TDC3K - Termination board



2908892

<https://www.phoenixcontact.com/us/products/2908892>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Migration board for converting TDC3000 to modern control platforms, digital output, 32 channel

## Your advantages

- Panel mount to existing TDC3000 chassis
- Compatible with existing pluggable field wiring connectors
- DSUB control side connection
- Terminal blocks for power supply

## Commercial data

Item number	2908892
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C421
Product key	DK2B8H
GTIN	4055626733098
Weight per piece (including packing)	525 g
Weight per piece (excluding packing)	500 g
Customs tariff number	85371098
Country of origin	US

# FLX-D37F/32CH/DO/TDC3K - Termination board



2908892

<https://www.phoenixcontact.com/us/products/2908892>

## Technical data

### Product properties

Product type	Interface module
--------------	------------------

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Electrical properties

Max. operating voltage $U_{max}$	30 V DC (Power supply)
Operating voltage	30 V DC
Max. current carrying capacity per branch	500 mA
Maximum power voltage feed	5 A (fuse limited)

Supported controller: HONEYWELL TDC3000

Suitable I/O card	TDOY22
-------------------	--------

### Connection data

#### Controller level

Connection method	D-SUB 37 female connector
Number of connections	2
Number of positions	37

#### Field level

Connection method	pluggable
-------------------	-----------

### Dimensions

#### Item dimensions

Width	307.3 mm
Height	120.7 mm
Depth	38.3 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Altitude	< 2000 m
Permissible humidity (operation)	< 90 %

### Mounting

Mounting position	any
-------------------	-----

### Notes

# FLX-D37F/32CH/DO/TDC3K - Termination board



2908892

<https://www.phoenixcontact.com/us/products/2908892>

## Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

# FLX-D37F/32CH/DO/TDC3K - Termination board





2908892


<https://www.phoenixcontact.com/us/products/2908892>

## Drawings

Dimensional drawing



Circuit diagram



# FLX-D37F/32CH/DO/TDC3K - Termination board





2908892


<https://www.phoenixcontact.com/us/products/2908892>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908892>

 <b>CSA</b> Approval ID: 108860_0_000				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

 <b>cUL Recognized</b> Approval ID: NRAQ8.E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

 <b>UL Recognized</b> Approval ID: NRAQ2 - E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

 <b>CSAus</b> Approval ID: 108860_0_000				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
Power	-	5 A	-	-
Signal	-	0.5 A	-	-

# FLX-D37F/32CH/DO/TDC3K - Termination board



2908892

<https://www.phoenixcontact.com/us/products/2908892>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FLX-D37F/32CH/DO/TDC3K - Termination board



2908892

<https://www.phoenixcontact.com/us/products/2908892>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	834ffd61-d0dd-42ed-99ea-b03dcbff397e

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)