

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Redundancy module, 5 V - 24 V DC, 2 x 10 A, 1 x 20 A.



## Product description

A safe redundant system is the result of the parallel connection of two power supply units which are decoupled from one another. To further increase system availability, UNO DIODE provides the solution: decoupling with diode.

## Your advantages

- Flexible mounting by simply snapping onto the DIN rail
- Save energy
- Rugged design
- Permanent monitoring of redundancy
- Consistent redundancy up to the load

## Commercial data

Item number	2905489
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM18
Product key	CMRU43
GTIN	4046356954594
Weight per piece (including packing)	232.1 g
Weight per piece (excluding packing)	200 g
Customs tariff number	85363030
Country of origin	VN

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Technical data

### Input data

#### DC operation

Nominal input voltage range	5 V DC ... 24 V DC
Input voltage range	4.5 V DC ... 30 V DC
Voltage type of supply voltage	DC
Reverse polarity protection	yes, < 60 V
Nominal input current ( $I_N$ )	2x 10 A (-25 °C ... 55 °C)
	1x 20 A (-25 °C ... 55 °C)
	2x 10 A (-25 °C ... 55 °C)
	1x 20 A (-25 °C ... 55 °C)
Transient surge protection	Varistor
Voltage drop, input/output	typ. 0.5 V

### Output data

Efficiency	> 97 %
Nominal output voltage	$U_{In} - 0,5 V$
Nominal output current ( $I_N$ )	1x 20 A (-25 °C ... 55 °C)
	2x 10 A (-25 °C ... 55 °C)
Derating	55 °C ... 70 °C (2.5 %/K)
Power loss nominal load max.	5 W ( $I_{OUT} = 10 A$ )

### Connection data

#### Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, max.	2.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, max.	2.5 mm <sup>2</sup>
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	14
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

Tightening torque max	0.6 Nm
-----------------------	--------

## Output

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	2.5 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section flexible max.	2.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule with plastic sleeve, max.	2.5 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, min.	0.2 mm <sup>2</sup>
Single conductor/flexible terminal point with ferrule without plastic sleeve, max.	2.5 mm <sup>2</sup>
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	14
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

## Electrical properties

Insulation voltage input, output / housing	500 V
--	-------

## Product properties

Product type	Redundancy module
Product family	UNO DIODE
MTBF (IEC 61709, SN 29500)	> 60600000 h (40 °C)
LED	no

## Insulation characteristics

Protection class	III
Degree of pollution	2

## Dimensions

Width	22.5 mm
Height	90 mm
Depth	84 mm
Horizontal pitch	1.3 Div.

## Installation dimensions

Installation distance right/left	5 mm / 5 mm
Installation distance top/bottom	30 mm / 30 mm

## Mounting

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

Mounting type	DIN rail: 35 mm
Assembly note	alignable: 0 mm horizontally, 30 mm vertically
Mounting position	horizontal DIN rail NS 35, EN 60715

## Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
Housing material	Metal
Housing material	PC
Foot latch material	POM (Polyoxymethylene)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (> 55 °C Derating: 2.5 %/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Climatic class	3K3 (in acc. with EN 60721)
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6) 15 Hz ... 150 Hz, 2.3g, 90 min.

## Standards and regulations

Standard - Electrical safety	IEC 62368-1 (SELV)
Standard – Safety extra-low voltage	IEC 62368-1 (SELV) und EN 60204-1 (PELV)

## Approvals

UL approvals	UL/C-UL listed UL 508 UL/C-UL Recognized UL 60950-1
--------------	--

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
EMC requirements for noise emission	EN 61000-6-3 EN 61000-6-4
EMC requirements for noise immunity	EN 61000-6-1 EN 61000-6-2

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Contact discharge	4 kV (Test Level 3)
Discharge in air	8 kV (Test Level 3)
Comments	Criterion B

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

## Electromagnetic HF field

Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 6 GHz
Test field strength	10 V/m (Test Level 3)
Comments	Criterion A

## Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

## Fast transients (burst)

Input	2 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion B

## Surge voltage load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Surge voltage load (surge)

Input	1 kV (Test Level 3 - symmetrical)
	2 kV (Test Level 4 - asymmetrical)
Output	1 kV (Test Level 2 - symmetrical)
	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion B

## Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

## Conducted interference

Input/output/signal	asymmetrical
Frequency range	0.15 MHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)

## Voltage dips

Standards/regulations	EN 61000-4-11
-----------------------	---------------

## Emitted interference

Standards/regulations	EN 61000-6-3
Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential

## Criteria

Criterion A	Normal operating behavior within the specified limits.
-------------	--

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

Criterion B

Temporary impairment to operational behavior that is corrected by the device itself.

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module




2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Drawings

Block diagram



# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2905489>



**cUL Recognized**  
Approval ID: FILE E 214596



**UL Recognized**  
Approval ID: FILE E 214596



**IECEE CB Scheme**  
Approval ID: DK-36263-UL



**EAC**  
Approval ID: RU C-DE.A\*30.B.01082



**UL Listed**  
Approval ID: E123528



**cUL Listed**  
Approval ID: E123528



**IECEE CB Scheme**  
Approval ID: NL2-021198

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Classifications

### ECLASS

ECLASS-13.0	27371010
ECLASS-15.0	27371010

### ETIM

ETIM 10.0	EC000683
-----------	----------

### UNSPSC

UNSPSC 21.0	32151500
-------------	----------

# UNO-DIODE/5-24DC/2X10/1X20 - Redundancy module



2905489

<https://www.phoenixcontact.com/us/products/2905489>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	Lead(CAS: 7439-92-1)
SCIP	f746016c-854c-4578-b552-fdfe1bb372bc

### EF3.1 Climate Change

CO2e kg	3.584 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)