

# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP power cabling, universal front adapter for connecting all common 20-pos. SIMATIC S7-300 I/O modules, via two cables each with a 10-pos. COMBI connector, pitch: 3.5 mm

## Commercial data

Item number	2905538
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DK232S
GTIN	4046356960823
Weight per piece (including packing)	333.33 g
Weight per piece (excluding packing)	333.33 g
Country of origin	DE

# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

## Technical data

### Product properties

Product type	Front adapter
--------------	---------------

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Electrical properties

Operating voltage (AC/DC)	≤ 250 V AC/DC
Nominal operating mode	100% operating factor
Current (per single-core wire, 40°C)	≤ 6 A
Current (per single-core wire, 60°C)	≤ 4 A
Current (Total current per cable, 40°C)	≤ 20 A
Current (Total current per cable, 60°C)	≤ 16 A
Rated insulation voltage	260 V
Rated surge voltage	4 kV (Basic insulation)

Supported controller: SIEMENS S7-300 / ET 200 M

Suitable I/O card	6ES7321-1BH02-0AA0
	6ES7321-1BH10-0AA0
	6ES7321-7BH01-0AB0
	6ES7321-1BH50-0AA0
	6ES7321-1CH20-0AA0
	6ES7321-1FH00-0AA0
	6ES7321-1FF01-0AA0
	6ES7322-1FL00-0AA0
	6ES7322-1BH01-0AA0
	6ES7322-1BH10-0AA0
	6ES7322-1FH00-0AA0
	6ES7322-1BF01-0AA0
	6ES7322-8BF00-0AB0
	6ES7322-1CF00-0AA0
	6ES7322-1FF01-0AA0
	6ES7322-1HH01-0AA0
	6ES7322-1HF01-0AA0
	6ES7323-1BH01-0AA0
	6ES7327-1BH00-0AB0
	6ES7331-7HF01-0AB0
	6ES7331-7KF02-0AB0
	6ES7331-7KB02-0AB0
	6ES7332-7ND02-0AB0
	6ES7332-5HD01-0AB0
6ES7332-5HB01-0AB0	

# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

	6ES7334-0CE01-0AA0
	6ES7334-0KE00-0AB0
	6ES7331-7TF01-0AB0
	6ES7332-8TF01-0AB0
	6ES7336-4GE00-0AB0

## Connection data

### Controller level

Connection method	Plug-in connection
Note	Can be plugged onto 20-pos. I/O modules

### Field level

Connection method	COMBICON connectors
Number of connections	2
Number of positions	10
Pitch	3.5 mm

## Dimensions

### Cable

Length	8 m
--------	-----

## Cable/line

Number of positions	10
Shielded	no
Conductor type	Round cable set
Conductor structure signal line	16x 1.80 mm
AWG signal line	21
Conductor cross-section	10x 0.5 mm <sup>2</sup>
Outer sheath, material	PVC
External sheath, color	gray
Conductor material	Bare Cu litz wires
Cable resistance	≤ 40 Ω/km
Insulation resistance	≥ 20 MΩ*km
Halogen-free	no
Flame resistance	UL VW-1

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C

## Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

	IEC 60664
--	-----------

## Mounting

Mounting position	any
-------------------	-----

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings


Dimensional drawing



	A	B
...4X10COMBI...	52	70
...2X10COMBI...		
...4X10 PT...	35	62
...2X10 PT...		

Circuit diagram

**S7 - 300**



# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

## Classifications

### ECLASS

ECLASS-13.0

27242292

### UNSPSC

UNSPSC 21.0

32151601

# VIP-PA-PWR/2X10 PT/ 8,0M/S7 - Front adapter



2905538

<https://www.phoenixcontact.com/us/products/2905538>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)