

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in miniature power relay in basic design, with power contact for high continuous currents, 1 changeover contact, input voltage 230 V AC

Commercial data

Item number	2906288
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	C460
Product key	DKF921
GTIN	4055626066912
Weight per piece (including packing)	14.5 g
Weight per piece (excluding packing)	14.5 g
Customs tariff number	85364900
Country of origin	AT

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Technical data

Product properties

Product type	Single relay
Product family	ESSENTIAL edition
Operating mode	100% operating factor
Mechanical service life	1x 10 ⁷ cycles

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	3

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Service life electrical	see diagram
Maximum power dissipation for nominal condition	0.4 W
Rated insulation voltage	250 V AC
Rated surge voltage	4 kV

Input data

Coil side

Nominal input voltage U _N	230 V AC
Input voltage range	184 V AC ... 333.5 V AC
Mains frequency	50/60 Hz
Drive and function	monostable
Drive (polarity)	non-polarized
Typical input current at U _N	3 mA
Typical response time	3 ms ... 12 ms (depending on phase relation)
Typical release time range	2 ms ... 9 ms (depending on phase relation)

Output data

Switching

Contact switching type	1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	5 V (At 24 mA)
Limiting continuous current	16 A
Maximum inrush current	30 A (300 ms)
Min. switching current	10 mA (at 12 V)

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Interrupting rating (ohmic load) max.	384 W (at 24 V DC)
	58 W (at 48 V DC)
	48 W (at 60 V DC)
	50 W (at 110 V DC)
	80 W (at 220 V DC)
	4000 VA (for 250 V AC)
Switching capacity	2 A (at 24 V, DC13)
	1.5 A (at 230 V, AC15)

Connection data

Connection method	Solder connection
-------------------	-------------------

Dimensions

Item dimensions	
Width	12.7 mm
Height	29 mm
Depth	15.7 mm

Material specifications

Color	white (RAL 9010)
-------	------------------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	RT II
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations


Standards/regulations	IEC 60664
	EN 61810-1

Mounting


Mounting type	Plug-in mounting
Mounting position	any

Drawings

Dimensional drawing




Diagram



- ① DC coils
- ② AC coils


Operating voltage range




- ① 250 V AC, ohmic load (DC coils)
- ② 250 V AC, ohmic load (AC coils)

Electrical service life

Diagram



Service life reduction factor with various cos phi



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures $\leq 0^{\circ}\text{C}$ must be prevented

Area B: Condensation at ambient temperatures $> 0^{\circ}\text{C}$ must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature $\leq 25^{\circ}\text{C}$.

Circuit diagram




REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Drilling plan/solder pad geometry



View from below

Grid spacing: 2.5 mm

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Approvals

📄 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2906288>



cUL Recognized

Approval ID: FILE E 228652



UL Recognized

Approval ID: FILE E 228652

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

REL-MR-BL-230AC/21HC - Single relay



2906288

<https://www.phoenixcontact.com/us/products/2906288>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.19 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com