

VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester



2906295

<https://www.phoenixcontact.com/us/products/2906295>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge arrester for 2-pos. isolated 600 V DC voltage systems, for DIN rail mounting, temperature-monitored protective elements, status message on the module.

The figure shows the VAL-MB-T1/T2
1500DC-PV/2+V version

Your advantages

- Space-saving installation, thanks to the compact design
- Double terminal block for safe and easy equipotential bonding connection
- Screw shafts with raised domes to ensure safe working
- Main connections with extended insertion funnels for increased resistance to creepage
- Visual display for checking the status directly on the device

Commercial data

Item number	2906295
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CL1341
GTIN	4055626063034
Weight per piece (including packing)	367.74 g
Weight per piece (excluding packing)	316.12 g
Country of origin	DE

VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester



2906295

<https://www.phoenixcontact.com/us/products/2906295>

Technical data

Product properties

Product type	PV arrester
Product family	VALVETRAB MB
IEC test classification	PV T2
Type	DIN rail module, one-piece
Environment	Indoor
Installation location of the disconnect device	Internal
Accessibility	Accessible
Connection configuration	Y configuration
End-of-life mode	OCM (Open-Circuit Failure Mode)
Surge protection fault message	optical
Number of ports	One


Insulation characteristics

Pollution degree	2
------------------	---

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	3 Nm
Stripping length	16 mm
Conductor cross-section flexible	2.5 mm ² ... 35 mm ²
Conductor cross-section AWG	14 ... 2

Dimensions

Dimensional drawing	
Width	71.2 mm
Height	120 mm
Depth	65.5 mm

Material specifications

Flammability rating according to UL 94	V-0
----------------------------------------	-----

Protective circuit

Mode of protection	(L+) - (L-)
	(L+) - PE
	(L-) - PE
Direction of action	(L+)-PE & (L-)-PE & (L+)-(L-)
Rated load current I _L	50 A

VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester



2906295

<https://www.phoenixcontact.com/us/products/2906295>

Protective conductor current I_{PE}	$\leq 20 \mu\text{A DC}$
	$\leq 370 \mu\text{A AC}$
Standby power consumption P_C	$\leq 16 \text{ mVA}$
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Total discharge current I_{Total} (8/20) μs	40 kA
Voltage protection level U_p	$\leq 2.9 \text{ kV}$
Residual voltage U_{res}	$\leq 2.9 \text{ kV}$ (at I_n)
	$\leq 2.1 \text{ kV}$ (at 3 kA)
	$\leq 2.4 \text{ kV}$ (at 6.25 kA)
	$\leq 2.5 \text{ kV}$ (at 10 kA)
	$\leq 2.8 \text{ kV}$ (at 15 kA)
	$\leq 3.6 \text{ kV}$ (at 40 kA)
Response time t_A	$\leq 25 \text{ ns}$

PV protective circuit

Connection configuration	Y configuration
End-of-life mode	OCM (Open-Circuit Failure Mode)

Protective circuit DC voltage side (DC)

Maximum continuous operating voltage U_{CPV}	800 V DC
Short-circuit current rating I_{SCPV}	2000 A
Open-circuit voltage U_{OCSTC}	$\leq 667 \text{ V DC}$
Maximum discharge current I_{max} (8/20) μs	40 kA
Response time t_A	$\leq 25 \text{ ns}$
Total discharge current I_{Total} (8/20) μs	40 kA
Insulation resistance R_{iso}	$> 5 \text{ G}\Omega$ (at 500 V DC)
Nominal discharge current I_n (8/20) μs	20 kA
Rated load current I_L	50 A
Continuous operating current I_{CPV}	$< 20 \mu\text{A}$
Maximum continuous operating voltage U_{CPV}	800 V DC
Short-circuit current rating I_{SCPV}	2000 A
Residual voltage U_{res}	$\leq 2.9 \text{ kV}$ (at I_n)
	$\leq 2.1 \text{ kV}$ (at 3 kA)
	$\leq 2.4 \text{ kV}$ (at 6.25 kA)
	$\leq 2.5 \text{ kV}$ (at 10 kA)
	$\leq 2.8 \text{ kV}$ (at 15 kA)
	$\leq 3.6 \text{ kV}$ (at 40 kA)
Protective conductor current I_{PE}	$\leq 20 \mu\text{A DC}$
	$\leq 370 \mu\text{A AC}$
Voltage protection level U_p	$\leq 2.9 \text{ kV}$
Standby power consumption P_C	$\leq 16 \text{ mVA}$

Environmental and real-life conditions

VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester



2906295

<https://www.phoenixcontact.com/us/products/2906295>

Ambient conditions

Degree of protection	IP20 (only when all terminal points are used)
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 6000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	50g (Half-sine / 11 ms / 3x ±X, ±Y, ±Z)
Vibration (operation)	5g (5 - 500 Hz/2.5 h/X, Y, Z)

Standards and regulations

Standards/specifications	EN 50539-11
Note	2013

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester




2906295

<https://www.phoenixcontact.com/us/products/2906295>

Drawings

Dimensional drawing




VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester

2906295

<https://www.phoenixcontact.com/us/products/2906295>



Circuit diagram



VAL-MB-T2 600DC-PV/2+V - Type 2 surge arrester



2906295

<https://www.phoenixcontact.com/us/products/2906295>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com