

1771-CARDEDGE40/2XD25F - Interface card



2906297

<https://www.phoenixcontact.com/us/products/2906297>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Allen-Bradley® PLC-5 migration board used to convert 1771 I/O and pre-wired 40-position swing arm (1771-WN) to 25-position (female) D-SUB sockets.

Your advantages

- Durable PCB designed to easily mount within 1771 chassis
- Card edge connection with locking tab
- Quick cable connection via two D-SUB 25 female connectors

Commercial data

Item number	2906297
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK2BZZ
GTIN	4055626365602
Weight per piece (including packing)	417.3 g
Weight per piece (excluding packing)	556.7 g
Customs tariff number	85366990
Country of origin	US

1771-CARDEGE40/2XD25F - Interface card



2906297

<https://www.phoenixcontact.com/us/products/2906297>

Technical data

Product properties

Product type	Interface module
Number of positions	40

Electrical properties

Nominal voltage U_N	max. 125 V AC/DC
Max. current carrying capacity per branch	2 A

Supported controller: ALLEN-BRADLEY PLC 5

Suitable I/O card	1771-IAN
	1771-IBN
	1771-ID16
	1771-IQ16
	1771-IVN
	1771-OBN
	1771-OD16
	1771-ODD
	1771-OQ16
	1771-OVN
	1771-OW16
	1771-OWN
	1771-OWNA
1771-VHSC	

Connection data

PCB edge contact

Number of positions	40
---------------------	----

Controller level

Connection method	D-SUB-25 female connector
Number of connections	2
Number of positions	25

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	254 mm
Height	143.5 mm
Depth	21.3 mm

1771-CARDEDGE40/2XD25F - Interface card



2906297

<https://www.phoenixcontact.com/us/products/2906297>

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

1771-CARDEDGE40/2XD25F - Interface card





2906297


<https://www.phoenixcontact.com/us/products/2906297>

Drawings

Dimensional drawing



Circuit diagram



1771-CARDEDGE40/2XD25F - Interface card



2906297

<https://www.phoenixcontact.com/us/products/2906297>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1771-CARDEGE40/2XD25F - Interface card



2906297

<https://www.phoenixcontact.com/us/products/2906297>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b4fa982b-170a-4f2c-81b7-a0b58382d6a9

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com