

# PLT-T3-230-P - Type 3 surge protection plug



2906495

<https://www.phoenixcontact.com/us/products/2906495>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Replacement plug for type 3 device protection from the PLUGTRAB T3 product range. 230 V nominal voltage.

## Commercial data

Item number	2906495
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	CLP311
GTIN	4055626082028
Weight per piece (including packing)	37.37 g
Weight per piece (excluding packing)	34 g
Country of origin	DE

# PLT-T3-230-P - Type 3 surge protection plug

2906495

<https://www.phoenixcontact.com/us/products/2906495>

## Technical data


### Product properties

Product type	Replacement plug
Type	Male
Number of positions	2
Surge protection fault message	optical

### Insulation characteristics

Overvoltage category	III
Pollution degree	2
IEC test classification	III
	T3
EN type	T3
Number of ports	One

### Dimensions

Dimensional drawing	
Width	17.5 mm
Height	44.8 mm
Depth	51.7 mm
Horizontal pitch	1 Div.

### Material specifications

Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6
Housing material	PA 6.6

### Protective circuit

Mode of protection	L-N L-PE N-PE
Direction of action	1L-N & N-PE
Nominal voltage $U_N$	230 V AC (TN-S) 230 V AC (TT - only in use with RCD)
Nominal frequency $f_N$	50 Hz (60 Hz)
Maximum continuous operating voltage $U_C$	255 V AC
Rated load current $I_L$	16 A AC (at 63 °C)
Protective conductor current $I_{PE}$	$\leq 5 \mu A$

# PLT-T3-230-P - Type 3 surge protection plug



2906495

<https://www.phoenixcontact.com/us/products/2906495>

Standby power consumption $P_C$	$\leq 350$ mVA
Reference test voltage $U_{REF}$	255 V AC
Nominal discharge current $I_n$ (8/20) $\mu$ s	3 kA
Combination wave $U_{OC}$	6 kV
Voltage protection level $U_p$ (L-N)	$\leq 1.25$ kV
Voltage protection level $U_p$ (L-PE)	$\leq 1.4$ kV
Voltage protection level $U_p$ (N-PE)	$\leq 1.4$ kV
TOV behavior at $U_T$ (L-N)	440 V AC (5 s / withstand mode) 440 V AC (120 min / withstand mode)
TOV behavior at $U_T$ (L-PE)	440 V AC (5 s / withstand mode) 440 V AC (120 min / withstand mode) 1455 V AC (200 ms / safe failure mode)
TOV behavior at $U_T$ (N-PE)	1200 V AC (200 ms / safe failure mode)
Response time $t_A$ (L-N)	$\leq 25$ ns
Response time $t_A$ (L-PE)	$\leq 100$ ns
Response time $t_A$ (N-PE)	$\leq 100$ ns
Short-circuit current rating $I_{SCCR}$	1.5 kA AC
Maximum backup fuse for through wiring	16 A (B)
Max. backup fuse with branch wiring	16 A (B)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	$\leq 2000$ m (amsl)
Permissible humidity (operation)	5 % ... 95 %

## Approvals

### UL specifications

Maximum continuous operating voltage MCOV	255 V AC
Nominal discharge current $I_n$	3 kA
Mode of protection	L-N L-G N-G
Power distribution system	Single phase
Nominal frequency	50/60 Hz
Measured limiting voltage MLV (L-N)	1500 V
Measured limiting voltage MLV (L-G)	1200 V
Measured limiting voltage MLV (N-G)	1200 V
SPD Type	4CA

## Standards and regulations

# PLT-T3-230-P - Type 3 surge protection plug



2906495

<https://www.phoenixcontact.com/us/products/2906495>

Standards/specifications	EN 61643-11
Note	2012

## Mounting

Mounting type	on base element
---------------	-----------------

# PLT-T3-230-P - Type 3 surge protection plug


2906495

<https://www.phoenixcontact.com/us/products/2906495>



## Drawings

Dimensional drawing




# PLT-T3-230-P - Type 3 surge protection plug

2906495

<https://www.phoenixcontact.com/us/products/2906495>



Circuit diagram



# PLT-T3-230-P - Type 3 surge protection plug



2906495

<https://www.phoenixcontact.com/us/products/2906495>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)