

# PLC-TR-1T-MUL-300M-PT - Timer relay



2910141

<https://www.phoenixcontact.com/us/products/2910141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-function timer relay with 4 functions in an ultra-narrow design, adjustable time range (0.1 s - 300 min), 1 changeover contact, Push-in connection

## Commercial data

Item number	2910141
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C442
Product key	DK62AH
GTIN	4055626430607
Weight per piece (including packing)	38.3 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85364900
Country of origin	DE

# PLC-TR-1T-MUL-300M-PT - Timer relay



2910141

<https://www.phoenixcontact.com/us/products/2910141>

## Technical data

### Product properties

Product type	Timer relay
Operating mode	100% operating factor
Mechanical service life	2x 10 <sup>7</sup> cycles

### Insulation characteristics

Overvoltage category	III
Pollution degree	2

### Electrical properties

Service life electrical	2x 10 <sup>5</sup> cycles
Nominal power consumption	0.45 W (at 24 V DC)
Rated insulation voltage	300 V AC
Rated surge voltage	6 kV

### Input data

Nominal power consumption	0.45 W (at 24 V DC)
Input voltage range	24 V DC (19.2 V DC ... 30 V DC)
Recovery time	50 ms
Setting range time	0.1 s ... 300 min (4 time end ranges)
Setting accuracy	≤ 2.5 % (of scale end value)
Repeat accuracy	≤ 0.5 % (of scale end value)

### Control

Connection name	Non-floating, terminals A1-B1
Control pulse length	≥ 50 ms

### Output data

#### Switching

Contact switching type	1 floating changeover contact
Maximum switching voltage	250 V AC
Interrupting rating (ohmic load) max.	1500 VA (6 A/250 V AC)
Output fuse	6.3 A (fast-blow)

### Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

### Signaling

# PLC-TR-1T-MUL-300M-PT - Timer relay



2910141

<https://www.phoenixcontact.com/us/products/2910141>

Status display	Green LED (POWER)
	Yellow LED (relay active)

## Dimensions

Width	6.2 mm
Height	80 mm
Depth	86 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA, self-extinguishing

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	15 % ... 85 %

## Approvals

### CE

Identification	CE-compliant
----------------	--------------

### UL, USA/Canada

Identification	UL/C-UL Listed UL 508
----------------	-----------------------

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2

### Noise emission

Standards/regulations	EN 61000-6-3
-----------------------	--------------

## Standards and regulations

Standards/regulations	IEC 61812-1
	IEC 60947-5-1

## Mounting

Mounting type	DIN rail mounting
Assembly note	on standard DIN rail NS 35 in accordance with EN 60715
Mounting position	any

# PLC-TR-1T-MUL-300M-PT - Timer relay



2910141

<https://www.phoenixcontact.com/us/products/2910141>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910141>



**DNV GL**

Approval ID: TAA00002RX



**UL Listed**

Approval ID: FILE E 172140



**cUL Listed**

Approval ID: FILE E 172140

**DNV**

Approval ID: TAE0000196

# PLC-TR-1T-MUL-300M-PT - Timer relay



2910141

<https://www.phoenixcontact.com/us/products/2910141>

## Classifications

### ECLASS

ECLASS-13.0	27371605
ECLASS-15.0	27371605

### ETIM

ETIM 10.0	EC001439
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2910141

<https://www.phoenixcontact.com/us/products/2910141>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	be72ca50-670a-4ce7-93ea-c13857bb3efe

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)