

# PACT RCP-D95-10M - Coil



2910323

<https://www.phoenixcontact.com/us/products/2910323>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

300 mm long Rogowski coil. The measuring coil diameter when installed is 95 mm. The Rogowski coil is used for AC current measurement for busbars and power lines.



## Commercial data

Item number	2910323
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C444
Product key	CMMA12
GTIN	4055626437576
Weight per piece (including packing)	357 g
Weight per piece (excluding packing)	357 g
Customs tariff number	90309000
Country of origin	DE

## Technical data

### Product properties

Product type	Rogowski coil
Product family	Rogowski coil
Set comprises	2910326 PACT RCP-4000A-1A-D95-10M

### Insulation characteristics

Pollution degree	2
------------------	---

### Electrical properties

#### Measuring coil

Conductor structure signal line	2x 0.22 mm (Signal (tinned))
	1x 0.22 mm (Shielding (tinned))
Insulation	double insulation
Rated insulation voltage	1000 V AC (rms CAT III)
	600 V AC (rms CAT IV)
Test voltage	10.45 kV DC (60 s)
Accuracy class	0.2 (IEC 61869-10: A1)

#### General

Converter type	Rogowski coil
----------------	---------------

### Input data

#### Frequency

Designation	Measuring coil
Frequency measuring range	40 Hz ... 20000 Hz

#### Current transformer

Converter type	Rogowski coil
----------------	---------------

### Output data

#### Signal

Designation	Measuring coil
Output signal (at 50 Hz)	100 mV (no load, at 1,000 A)
Output voltage (in no-load operation)	$V_{OUT} = M \cdot dI/dt$
Output voltage (sinusoidal, in no-load operation)	100 mV ( $V_{OUT} = 2 \cdot \pi \cdot M \cdot f \cdot I$ (M = 0.318 $\mu$ H; example: At 50 Hz; I = 1,000 A))

### Dimensions

#### Measuring coil

Length	300 mm
Diameter	8.3 mm $\pm$ 0.2 mm

# PACT RCP-D95-10M - Coil



2910323

<https://www.phoenixcontact.com/us/products/2910323>

## Measuring coil when installed

Diameter	95 mm
----------	-------

## Signal line

Length	10 m
--------	------

## Material specifications

Housing material	PC
Coil material	Elastollan

## Environmental and real-life conditions

### Ambient conditions

Measuring coil degree of protection	IP54 (not assessed by UL)
Ambient temperature (operation) (Measuring coil)	-30 °C ... 80 °C (Measuring coil)
Ambient temperature (storage/transport)	-40 °C ... 80 °C (Measuring coil)
Altitude	< 2000 m
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

## Approvals

### CMIM

Certificate	CMIM-compliant
-------------	----------------

### UL, USA/Canada

Identification	UL 61010 Recognized
Note	Measuring coil

## Standards and regulations

Standards/regulations	IEC 61010-2-030
	IEC 61869-10

# PACT RCP-D95-10M - Coil

2910323

<https://www.phoenixcontact.com/us/products/2910323>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910323>



**cUL Recognized**  
Approval ID: FILE E 357804



**UL Recognized**  
Approval ID: FILE E 357804

# PACT RCP-D95-10M - Coil

2910323

<https://www.phoenixcontact.com/us/products/2910323>



## Classifications

### ECLASS

ECLASS-13.0	27210992
ECLASS-15.0	27210992

### ETIM

ETIM 10.0	EC002498
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

# PACT RCP-D95-10M - Coil



2910323

<https://www.phoenixcontact.com/us/products/2910323>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)