

# UM-D25SUB/M/DO - Output module



2907015

<https://www.phoenixcontact.com/us/products/2907015>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Digital VARIOFACE output module with COMBICON screw connection and a 25-pos. D-SUB pin strip for ABB S 800 I/O modules.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2907015       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | DK2A82        |
| GTIN                                 | 4055626157306 |
| Weight per piece (including packing) | 303 g         |
| Weight per piece (excluding packing) | 303 g         |
| Country of origin                    | DE            |

# UM-D25SUB/M/DO - Output module



2907015

<https://www.phoenixcontact.com/us/products/2907015>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Interface module |
|--------------|------------------|

#### Insulation characteristics: Air clearances and creepage distances

|                      |                       |
|----------------------|-----------------------|
| Insulation           | Functional insulation |
| Overvoltage category | II                    |
| Pollution degree     | 2                     |

### Electrical properties

|   |            |
|---|------------|
| Nominal voltage $U_N$                     | 25 V AC/DC |
| Max. current carrying capacity per branch | 1 A        |
| Max. total current of all branches        | 2.5 A      |

#### Air clearances and creepage distances

|                          |                         |
|--------------------------|-------------------------|
| Rated insulation voltage | 50 V                    |
| Rated surge voltage      | 0.5 kV (1.2/50 $\mu$ s) |

### Connection data

#### Field level

|                                  |   |
|----------------------------------|---|
| Connection in acc. with standard | IEC / EN                                    |
| Connection method                | Screw connection                            |
| Number of positions              | 52  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |

#### Controller level

|                       |                 |
|-----------------------|-----------------|
| Connection method     | D-SUB pin strip |
| Number of connections | 1               |
| Number of positions   | 25              |

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Dimensions

#### Item dimensions

|        |        |
|--------|--------|
| Width  | 139 mm |
| Height | 90 mm  |
| Depth  | 65 mm  |

### Material specifications

# UM-D25SUB/M/DO - Output module



2907015

<https://www.phoenixcontact.com/us/products/2907015>

|                             |                  |
|-----------------------------|------------------|
| Color                       | green (RAL 6021) |
| Housing insulation material | PVC              |

## Environmental and real-life conditions

### Ambient conditions

|  |                                |
|--|--------------------------------|
| Degree of protection                         | IP00                           |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation)              | -20 °C ... 50 °C               |
| Altitude                                     | ≤ 2000 m                       |

## Standards and regulations

### Air clearances and creepage distances

|                       |                       |
|-----------------------|-----------------------|
| Standards/regulations | DIN EN 50178: 1998-04 |
|-----------------------|-----------------------|

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

# UM-D25SUB/M/DO - Output module



2907015

<https://www.phoenixcontact.com/us/products/2907015>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UM-D25SUB/M/DO - Output module



2907015

<https://www.phoenixcontact.com/us/products/2907015>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)