

PT-IQ-3-BE-UT - Surge protection base-element



2910419

<https://www.phoenixcontact.com/us/products/2910419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Base element for PLUGTRAB PT-IQ protective plug (3-HF, 2X1,1X2)



Product description

DIN rail connector not included with delivery of PT-IQ basic element (PT-IQ-17,5-TBUS-5-2.0). Required DIN rail connectors must be ordered separately.

Commercial data

Item number	2910419
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	CL2151
GTIN	4055626461564
Weight per piece (including packing)	71.8 g
Weight per piece (excluding packing)	63 g
Country of origin	DE

PT-IQ-3-BE-UT - Surge protection base-element

2910419

<https://www.phoenixcontact.com/us/products/2910419>

Technical data

Product properties

Product type	Base element
Product family	PLUGTRAB IQ
Type	Base element, DIN rail mounting
Number of positions	3
Surge protection fault message	none

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal voltage U_N	48 V DC
-----------------------	---------

Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	17.7 mm
Height	91.1 mm
Depth	51.6 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	1 Div.

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V-0
Housing material	PA 6.6

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

PT-IQ-3-BE-UT - Surge protection base-element



2910419

<https://www.phoenixcontact.com/us/products/2910419>

Nominal voltage U_N	48 V DC
Maximum continuous operating voltage U_C	53 V DC
	37 V AC
Rated current	300 mA (53 V DC)
	1 A (40 °C, 30 V DC)
Resistance per path	1.2 Ω \pm 5 %
Max. required back-up fuse	1 A (FF, \leq 30 V DC)
	315 mA (FF, 53 V DC)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	\leq 4000 m (amsl)

Standards and regulations

Standards/specifications	IEC 61643-21
Note	2000 + A1:2008, modified
Standards/specifications	EN 61643-21
Note	2001 + A1:2009
Standards/specifications	EN 61000-6-3
Note	2007 + A1:2011
Standards/specifications	EN 61000-6-2
Note	2005

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

PT-IQ-3-BE-UT - Surge protection base-element




2910419


<https://www.phoenixcontact.com/us/products/2910419>

Drawings

Dimensional drawing



Diagram



PT-IQ-3-BE-UT - Surge protection base-element



2910419

<https://www.phoenixcontact.com/us/products/2910419>

Classifications

ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

ETIM

ETIM 10.0	EC001466
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

2910419

<https://www.phoenixcontact.com/us/products/2910419>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	20bb2a75-6b46-4c09-a34a-95d118562f5f

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com