

UM 108-4XD15SUB/S/SC068 - Termination board




2907442

<https://www.phoenixcontact.com/us/products/2907442>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Interface module, for tapping serial data transmission, fitted with a D-SUB 15-pos. socket strip, **three** D-SUB 15-pos. strips, and a cross switch



Commercial data

Item number	2907442
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C429
Product key	DK2A82
GTIN	4055626204833
Weight per piece (including packing)	144 g
Weight per piece (excluding packing)	144 g
Customs tariff number	85366990
Country of origin	DE

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible current	150 mA (via switch)
Nominal voltage U_N	25 V AC/DC
Max. current carrying capacity per branch	1 A

Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 μ s)

Connection data

D-SUB connection

Connection method	D-SUB-15 socket
Number of connections	1
Number of positions	15

D-SUB connection

Connection method	D-SUB-15 male connector
Number of connections	3
Number of positions	15

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	49 mm
Height	126 mm
Depth	50 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PVC

Environmental and real-life conditions

UM 108-4XD15SUB/S/SC068 - Termination board



2907442

<https://www.phoenixcontact.com/us/products/2907442>

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

Standards and regulations

Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

UM 108-4XD15SUB/S/SC068 - Termination board



2907442

<https://www.phoenixcontact.com/us/products/2907442>

Classifications

UNSPSC

UNSPSC 21.0	39121432
-------------	----------

UM 108-4XD15SUB/S/SC068 - Termination board



2907442

<https://www.phoenixcontact.com/us/products/2907442>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com