

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LCD monitor with touch screen, 15" display, with digital image transmission, IP65 housing



## Commercial data

Item number	2913302
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	DR12
Product key	DRBBAD
GTIN	4046356324632
Weight per piece (including packing)	4.44 kg
Weight per piece (excluding packing)	4.44 kg
Customs tariff number	85299020
Country of origin	DE

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

## Technical data

### Product properties

Product type	Monitor
--------------	---------

### Computer data

Processor	without processor
Operating system	without operating system
RAM	without RAM
Data storage system	without data storage
Cooling	passive
Slots	without slots
Optical drive	without drive

### Display

Display type	38.1 cm / 15"-TFT
Screen resolution	1024 x 768 Pixel(s) (XGA)
Touch technology	Resistive industrial touch screen
Display lighting type	CCFL
Brightness	330 cd/m <sup>2</sup> typical (adjustable)

### System properties

User software	without user software
---------------	-----------------------

### Electrical properties

#### Supply

Power supply unit	230 V AC
-------------------	----------

### Interfaces

Interfaces	1x DVI-D
Network	without network

### Dimensions

Width	395 mm
Height	292 mm
Depth	65 mm

#### External dimensions

Width / Height / Depth	395 mm / 292 mm / 65 mm
------------------------	-------------------------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	5 °C ... 45 °C

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

Ambient temperature (storage/transport)	-20 °C ... 60 °C
Permissible humidity (operation)	10 % ... 85 %
Permissible humidity (storage/transport)	10 % ... 85 %

## Mounting

Mounting type	LCD monitor for mounting in the front panel
---------------	---

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

## Environmental product compliance

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)