

UM 25-PROFIL 100CM - Profile



2915795

<https://www.phoenixcontact.com/us/products/2915795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Press-drawn section housings, DIN rail mounting, Basic profile, profile width (internal): 22 mm, profile width (external): 24.8 mm, length: 1000 mm, Note: required profile length = PCB length - 3 mm

Your advantages

- Flexible size and shape
- Fast mounting
- Inexpensive as a result of reducing the number of separate housing parts

Commercial data

Item number	2915795
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDBA
GTIN	4046356178686
Weight per piece (including packing)	200 g
Weight per piece (excluding packing)	200 g
Customs tariff number	39162000
Country of origin	DE

UM 25-PROFIL 100CM - Profile

2915795


<https://www.phoenixcontact.com/us/products/2915795>

Technical data

Product properties

Product type	Component housing lower part
Housing type	Press-drawn section housings
Housing type	Extruded profile housings
Housing series	UM
Product family	UM25
Ventilation openings present	no

Dimensions

Dimensional drawing	
Length	1 m

External dimensions

Profile width (external)	24.8 mm
--------------------------	---------

Internal dimensions

Profile width (internal)	22 mm
--------------------------	-------

Material specifications

Color (Profile)	green (RAL 6021)
Material Profile	PVC
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


UM 25-PROFIL 100CM - Profile

2915795

<https://www.phoenixcontact.com/us/products/2915795>



Drawings



UM 25-PROFIL 100CM - Profile



2915795

<https://www.phoenixcontact.com/us/products/2915795>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 10.0	EC002779
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 25-PROFIL 100CM - Profile



2915795

<https://www.phoenixcontact.com/us/products/2915795>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com