

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i NAMUR isolation amplifier. For operating proximity sensors and switches in a potentially explosive area. The signals are transmitted by a relay output (changeover contact) to a safe area. Line fault detection (LFD), 3-way isolation, SIL 2.

Your advantages

- Power supply and error indication possible via DIN rail connector
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Up to SIL 2 in accordance with EN 61508
- Line fault detection (LFD), can be activated/deactivated, error indicated by flashing red LED with de-excitation of output relay
- Input for NAMUR proximity sensors (EN 60947-5-6), floating contacts or contacts with resistance circuit, [Ex ia] IIC
- Signal output relay (changeover contact)
- Direction of operation can be selected (operating or closed circuit current behavior)
- 3-way electrical isolation
- LED indicators for supply voltage, switching state, and malfunction in accordance with NAMUR NE 44

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2924045 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C430 |
| Product key | DK1213 |
| GTIN | 4046356338059 |
| Weight per piece (including packing) | 170 g |
| Weight per piece (excluding packing) | 131.5 g |
| Customs tariff number | 85365019 |
| Country of origin | DE |

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Technical data

Product properties

| | |
|-----------------|----------------------------|
| Product type | Isolating switch amplifier |
| Product family | MACX Analog |
| Application | Digital IN |
| No. of channels | 1 |
| Configuration | DIP switches |

System properties

Functionality

| | |
|---------------|--------------|
| Configuration | DIP switches |
|---------------|--------------|

Electrical properties

| | |
|---|-----------------|
| Electrical isolation | 3-way isolation |
| Electrical isolation between input and output | yes |
| Maximum power dissipation for nominal condition | < 650 mW |

Electrical isolation

| | |
|--------------|-------------------------|
| Test voltage | 2.5 kV AC (50 Hz, 60 s) |
|--------------|-------------------------|

Electrical isolation Input/output IEC/EN 60079-11

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 375 V _{PP} |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical isolation Input/output/supply, DIN rail connector IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Overvoltage category | II |
| Pollution degree | 2 |
| Insulation | Safe isolation |

Electrical isolation Output/input, supply, TBUS IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Overvoltage category | III |
| Pollution degree | 2 |
| Insulation | Safe isolation |

Electrical isolation Input/supply, DIN rail connector IEC/EN 60079-11

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 375 V _{PP} |
| Overvoltage category | II |

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

| | |
|------------------|---|
| Pollution degree | 2 |
|------------------|---|

Supply

| | |
|--------------------------|-------------------------|
| Nominal supply voltage | 24 V DC -20 % ... +25 % |
| Supply voltage range | 19.2 V DC ... 30 V DC |
| Max. current consumption | 21 mA (24 V DC) |
| Power dissipation | < 1 W |
| Power consumption | < 1 W |

Input data

Signal: NAMUR

| | |
|---|--|
| Description of the input | intrinsically safe |
| Number of inputs | 1 |
| Available input sources | NAMUR proximity sensors (IEC/EN 60947-5-6) |
| | floating switch contacts |
| | Switch contacts with resistance circuit |
| Switching threshold "0" signal current | < 1.2 mA (blocking) |
| Switching threshold "1" signal, current | > 2.1 mA (conductive) |
| Short-circuit current | 8 mA |
| Switching hysteresis | < 0.2 mA |
| Line fault detection | < 0.05 mA ... 0.35 mA (Line break) |
| | < 100 Ω ... 360 Ω (Short circuit) |
| | Activated /deactivated via DIP switch |
| Open-circuit voltage | 8 V DC |

Output data

Switching: Relay

| | |
|---------------------------|---------------------------------------|
| Contact switching type | 1 changeover contact |
| Contact material | AgSnO ₂ , hard gold-plated |
| Maximum switching voltage | 250 V AC (2 A) |
| | 120 V DC (0.2 A) |
| | 30 V DC (2 A) |
| Maximum switching power | 500 VA |
| Recommended minimum load | 5 V / 10 mA |
| Switching frequency | ≤ 20 Hz (without load) |

Signal

| | |
|-------------------|---|
| Number of outputs | 1 |
|-------------------|---|

Connection data

| | |
|----------------------------------|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

| | |
|---|---|
| Conductor cross-section flexible (2 conductors with same cross section) | 0.25 mm ² ... 0.34 mm ² (TWIN ferrule without plastic sleeve) |
| | 0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve) |
| Conductor cross-section AWG | 24 ... 14 |
| | 24 ... 22 (TWIN ferrule without plastic sleeve) |
| | 20 ... 16 (TWIN ferrule with plastic sleeve) |

Ex data

| | |
|-----------------------|----------|
| Ex installation (EPL) | Gc |
| | Div. 2 |
| Ex i circuits (EPL) | [Ga] |
| | [Da] |
| | [Ma] |
| | [Div. 1] |

Safety data

| | |
|--|--|
| Max. internal inductance L_i | negligible |
| Max. internal capacitance C_i | 11 nF |
| Max. output voltage U_o | 9.6 V |
| Max. output current I_o | 10 mA |
| Max. output power P_o | 25 mW |
| Safety-related maximum voltage U_m | 253 V AC |
| | 125 V DC |
| I/A/I (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 1000 mH / 210 μ F |
| IIB/IIIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 1000 mH / 26 μ F |
| IIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 300 mH / 3.6 μ F |
| IIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 100 mH / 500 nF, 50 mH / 570 nF, 5 mH / 590 nF |
| I/IIIB/IIA/IIIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 100 mH / 1 μ F |

Interfaces

Data

| | |
|-----------------|---|
| No. of channels | 0 |
|-----------------|---|

Signaling

| | |
|----------------|------------------------------|
| Status display | Green LED (supply voltage) |
| | LED yellow (switching state) |
| | Red LED (line errors) |

Dimensions

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

| | |
|---------------------|--|
| Dimensional drawing | |
| Width | 12.5 mm |
| Height | 107.9 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
| Housing material | PA 6.6-FR |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 (not assessed by UL) |
| Ambient temperature (operation) | -40 °C ... 60 °C (Any mounting position) -40 °C ... 70 °C (Derating) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |

Altitude range (≤ 2000 m)

| | |
|---------------------------------|--|
| Altitude | ≤ 2000 m (The technical data refers to altitudes ≤2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 60 °C -40 °C ... 70 °C (Derating) |
| Rated insulation voltage | 253 V AC (Power supply, input / output) 125 V DC (Power supply, input / output) |

Altitude range (≤ 3000 m)

| | |
|---------------------------------|--|
| Height range | > 2000 m ... 3000 m |
| Ambient temperature (operation) | -40 °C ... 54 °C -40 °C ... 63 °C (Derating) |
| Rated insulation voltage | 190 V AC (Power supply, input / output) 110 V DC (Power supply, input / output) |

Altitude range (≤ 4000 m)

| | |
|---------------------------------|---------------------|
| Height range | > 3000 m ... 4000 m |
| Ambient temperature (operation) | -40 °C ... 48 °C |

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

| | |
|---------------------------------|---|
| | -40 °C ... 56 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |
| Altitude range (≤ 5000 m) | |
| Height range | > 4000 m ... 5000 m |
| Ambient temperature (operation) | -40 °C ... 42 °C |
| | -40 °C ... 49 °C (Derating) |
| Rated insulation voltage | 60 V AC/DC (Power supply, input / output) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
| Note | and EN 61326 |

ATEX

| | |
|----------------|---|
| Identification | Ⓜ II (1) G [Ex ia Ga] IIC |
| | Ⓜ II (1) D [Ex ia Da] IIIC |
| | Ⓜ II 3 (1) G Ex ec [ia Ga] nC IIC T4 Gc |
| | Ⓜ I (M1) [Ex ia Ma] I |
| Certificate | IBExU 07 ATEX 1069 X |

IECEX

| | |
|----------------|----------------------------|
| Identification | [Ex ia Ga] IIC |
| | [Ex ia Da] IIIC |
| | Ex ec [ia Ga] nC IIC T4 Gc |
| | [Ex ia Ma] I |
| Certificate | IECEX IBE 08.0001X |

CCC / China-Ex

| | |
|----------------|----------------------------|
| Identification | [Ex ia Ga] IIC |
| | [Ex ia Da] IIIC |
| | Ex ec nC [ia Ga] IIC T4 Gc |
| Certificate | 2022122316115975 |

UL, USA/Canada

| | |
|----------------|---|
| Identification | UL 61010 Listed |
| | Class I, Div. 2, Groups A, B, C, D T4 |
| | Class I, Div. 2, Groups IIC, IIB, IIA T4 |
| | Associated apparatus for use in Class I, Division 1, Groups A,B,C,D |
| | Associated apparatus for use in Class II, Div.1 Groups E,F,G |
| | Associated apparatus for use in Class III, Division 1 |
| | Associated apparatus for use in Class I, Zone 0,1,2, Groups IIC,IIB,IIA |
| Certificate | Ⓜ-Ⓜ C.D.-No 83104549 |

KC-s

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

| | |
|----------------|-----------------|
| Identification | [Ex ia] IIC/IIB |
| Certificate | 17-KA4BO-0408X |

Shipbuilding approval

| | |
|-------------|-------------------|
| Certificate | DNV GL TAA00000AG |
|-------------|-------------------|

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|-----------------------|
| Identification | 2 |
| Certificate | IN-AT-AS-MRL-24-00163 |

Systematic Capability

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

INMETRO

| | |
|----------------|----------------------------|
| Identification | [Ex ia Ga] IIC |
| | [Ex ia Da] IIC |
| | Ex ec nC [ia Ga] IIC T4 Gc |
| | [Ex ia Ma] I |
| Certificate | DNV 18.0114 X |

Shipbuilding data

| | |
|-------------|---|
| Temperature | B |
| Humidity | B |
| Vibration | A |
| EMC | B |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

EMC data

| | |
|----------------|--------------|
| Noise immunity | EN 61000-6-2 |
| | EN 61326 |

Standards and regulations

| | |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

GB Standard

| | |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
| | GB/T 3836.3 |
| | GB/T 3836.4 |
| | GB/T 3836.8 |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Drawings

Dimensional drawing




MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Block diagram



MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2924045>

 **UL Listed**
Approval ID: E330267


 **cUL Listed**
Approval ID: E330267


Functional Safety
Approval ID: 07-06-39 R005 V2R2

DNV
Approval ID: TAA00000AG

ECAS
Approval ID: 163683 E25 08 169506

TUEV Austria FS
Approval ID: IN-AT-AS-24-00163

 **EAC Ex**
Approval ID: TR TS_S_103.01.00078

 **IECEx**
Approval ID: IECEx IBE 08.0001X

 **cUL Listed**
Approval ID: E199827

 **UL Listed**
Approval ID: E199827

 **ATEX**
Approval ID: IBEU07ATEX1069

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

INMETRO

Approval ID: DNV 18.0114 X



KC-s

Approval ID: 17-KA4BO-0408X



CCC

Approval ID: 2022122316115975

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210121 |
| ECLASS-15.0 | 27210121 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001485 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

MACX MCR-EX-SL-NAM-R-SP - Isolation switch amplifier



2924045

<https://www.phoenixcontact.com/us/products/2924045>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | 501c891d-a118-4e8b-bbb5-3e252726e051 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 4.445 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com