

# TTC-6-FMRS-UT - Remote signaling set



2907810

<https://www.phoenixcontact.com/us/products/2907810>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module set for the optical monitoring and floating remote signaling of adjacent surge protective devices in the TERMITRAB complete or CLIXTRAB product family. Suitable for directly grounded DIN rails.

## Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Collective remote monitoring of up to 40 protective devices via optical monitoring
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features

## Commercial data

Item number	2907810
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL23
Product key	CL226Z
GTIN	4055626244402
Weight per piece (including packing)	83.3 g
Weight per piece (excluding packing)	67.5 g
Customs tariff number	85363010
Country of origin	DE

# TTC-6-FMRS-UT - Remote signaling set



2907810

<https://www.phoenixcontact.com/us/products/2907810>

## Technical data

### Product properties

Product type	Remote signaling set
Product family	TERMITRAB complete
Type	DIN rail module, one-piece

### Insulation characteristics

Pollution degree	2
------------------	---

### Electrical properties

#### Indicator/remote signaling

Switching function	N/C contact 2.5 Ω
--------------------	-------------------

#### Supply: Status indicator/remote signaling

Operating voltage	10 V DC ... 36 V DC
Operating current	30 mA DC (24 V) 60 mA DC (10 V)


### Connection data

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Ex data

Altitude	≤ 2000 m (amsl)
----------	-----------------

### Dimensions

Dimensional drawing	
Width	6.2 mm +0.1 mm
Height	105.8 mm
Depth	83.5 mm (incl. DIN rail 7.5 mm)

### Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V-0

# TTC-6-FMRS-UT - Remote signaling set



2907810

<https://www.phoenixcontact.com/us/products/2907810>

Insulating material	PBT
Housing material	PBT

## Protective circuit

Surge protection fault message	Optical, remote indicator contact
--------------------------------	-----------------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 4000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %

## Approvals

### Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D T4A
------------------	--

## Standards and regulations

Standards/specifications	EN 61000-6-2
Note	2005
Standards/specifications	EN 61000-6-3
Note	2007 + A1:2011
Standards/specifications	EN IEC 60079-0
Note	2018
Standards/specifications	EN IEC 60079-7
Note	2015 + A1:2018
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-7
Note	2017

## Mounting

Mounting type	DIN rail: TH 35 - 7.5 mm
---------------	--------------------------


# TTC-6-FMRS-UT - Remote signaling set

2907810


<https://www.phoenixcontact.com/us/products/2907810>

## Drawings

Dimensional drawing



Circuit diagram



# TTC-6-FMRS-UT - Remote signaling set



2907810


<https://www.phoenixcontact.com/us/products/2907810>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907810>


 **CSA**  
Approval ID: 70136717


 **DNV GL**  
Approval ID: TAE000027G


 **UL Listed**  
Approval ID: FILE E 138168


 **CSAus**  
Approval ID: 70136717

**UAE-RoHS**  
Approval ID: 22-06-16192

 **cUL Listed**  
Approval ID: FILE E 333250

 **IECEX**  
Approval ID: IECEX BVS 21.0057X

 **ATEX**  
Approval ID: BVS 21 ATEX E 052 X

 **cULus Listed**  
Approval ID: File E 333250

# TTC-6-FMRS-UT - Remote signaling set



2907810

<https://www.phoenixcontact.com/us/products/2907810>

## Classifications

### ECLASS

ECLASS-13.0	27171501
ECLASS-15.0	27171501

### ETIM

ETIM 10.0	EC001466
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# TTC-6-FMRS-UT - Remote signaling set



2907810

<https://www.phoenixcontact.com/us/products/2907810>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7)
SCIP	11abee79-7d00-43f8-8b6d-e07893bd233f

### EF3.1 Climate Change

CO2e kg	3.207 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)