

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Replacement battery for UPS-BAT/VRLA... battery modules



## Commercial data

Item number	2908237
Packing unit	1 pc
Sales key	CM24
Product key	CMUEV3
GTIN	4055626297750
Weight per piece (including packing)	25,500 g
Weight per piece (excluding packing)	25,200 g
Customs tariff number	85072080
Country of origin	CN

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

## Technical data

### Input data

Input voltage	2x 12 V DC
---------------	------------

### Energy storage

Nominal capacity	38 Ah
Battery module service life	10 Years ... 12 Years (20 °C)
Latest startup date (battery only)	12 Months (0 °C ... 20 °C)
Latest startup (battery only) - range	9 Months ... 12 Months (20 °C ... 30 °C)
	6 Months ... 9 Months (30 °C ... 40 °C)
Battery technology	VRLA-AGM
Accumulator type	Panasonic LC-P1238APG
IQ technology	no

### Product properties

Product type	Battery
Product family	Replacement battery
IQ technology	no

### Dimensions

Width	330 mm
Height	175 mm
Depth	175 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C
Max. permissible relative humidity (operation)	≤ 95 %

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

## Classifications

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# UPS-BAT-KIT-VRLA 2X12V/38AH - Uninterruptible power supply replacement battery



2908237

<https://www.phoenixcontact.com/us/products/2908237>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### China RoHS

Environment friendly use period (EFUP)	EFUP-6 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)